

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742959

Luminaire Tested: LD4D15D010-EU4DR2015309024-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P742959
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR2015309024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1306.8 lumens
Efficiency: N/A
Efficacy: 82.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742959
CATALOG NUMBER: LD4D15D010-EU4DR2015309024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P742959

CATALOG NUMBER: LD4D15D010-EU4DR2015309024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	812681
5°	733198
10°	411511
15°	209172
20°	88565
25°	40881
30°	21637
35°	11658
40°	6233
45°	3678
50°	2142
55°	1143
60°	721
65°	517
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3678 cd/sqm



TEST NUMBER: P742959

CATALOG NUMBER: LD4D15D010-EU4DR2015309024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	529.6	40.5
10°-20°	521.5	39.9
20°-30°	170.3	13.0
30°-40°	58.0	4.4
40°-50°	19.5	1.5
50°-60°	5.9	0.4
60°-70°	1.9	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1221.4	93.5
0°-40°	1279.4	97.9
0°-60°	1304.7	99.8
0°-90°	1306.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1306.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7438	
5°	6685	530
15°	1849	521
25°	339	170
35°	87	58
45°	24	19
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P742959

CATALOG NUMBER: LD4D15D010-EU4DR2015309024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	7438.0
0.5°	7438.0
1°	7428.8
1.5°	7410.2
2°	7376.5
2.5°	7331.4
3°	7267.8
3.5°	7179.1
4°	7047.3
4.5°	6887.0
5°	6685.0
5.5°	6419.4
6°	6147.2
6.5°	5835.2
7°	5529.9
7.5°	5172.2
8°	4852.9
8.5°	4531.7
9°	4235.0
9.5°	3962.8
10°	3709.1
12.5°	2663.3
15°	1849.2
17.5°	1208.1
20°	761.7
22.5°	493.4
25°	339.1
27.5°	238.4
30°	171.5
32.5°	123.2
35°	87.4
37.5°	60.9
40°	43.7
42.5°	31.8
45°	23.8
47.5°	18.5
50°	12.6
52.5°	7.9
55°	6.0
57.5°	4.6
60°	3.3
62.5°	2.6
65°	2.0



TEST NUMBER: P742959
CATALOG NUMBER: LD4D15D010-EU4DR2015309024-4LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.3
70°		0.7

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)