

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: PORTFOLIO

Report Number: P494367

Luminaire Tested: **LDA2B059730R70D010 2LBDLC1MMS**

Issue Date: 3/9/2021

This test was performed under the Supervised Manufacturer's Testing Program. The results of this test have not been influenced by sources from within Cooper Lighting Solutions or from external interests.



**Test Information**

Test Method: LM-79-08  
Report Number: P494367  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-2011-037-81)  
Test Lab: INNOVATION CENTER  
Issue Date: 3/9/2021  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: PORTFOLIO  
Catalog Number: LDA2B059730R70D010 2LBDLC1MMS  
Description: 500 LUMEN 2IN ADJUSTABLE LED LUMINAIRE WITH 97 CRI LEDS AND 3000K CCT LEDS  
Light Source: -  
Ballast/Driver: -

Luminaire Equipment: Sample No.    Condition    Description

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 564.5 lumens  
Efficiency: N/A  
Efficacy: 80.6 lumens/watt  
Spacing Criteria (0/90/45): 1.12 / 1.12 / 1.06  
Luminous Opening: Circular (Dia: 0.17' x H: 0')  
CIE Type: Direct

Input Watts (W): 7  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT

TEST NUMBER: P494367

CATALOG NUMBER: LDA2B059730R70D010 2LBDLC1MMS

### Luminous Intensity Polar Plot





TEST NUMBER: P494367

CATALOG NUMBER: LDA2B059730R70D010 2LBDLC1MMS

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111		106	106	106		102	102	102	100
1	113	110	108	105	111	108	106	103	104	102	100		100	99	97		97	96	94	93
2	107	102	97	94	105	100	96	93	97	93	91		94	91	89		91	89	87	85
3	101	94	89	84	99	93	88	84	90	86	82		87	84	81		85	82	80	78
4	95	87	81	76	93	86	80	76	84	79	75		82	77	74		80	76	73	72
5	90	81	74	70	88	80	74	69	78	73	69		76	72	68		74	71	67	66
6	85	75	68	64	83	74	68	63	72	67	63		71	66	63		70	65	62	61
7	80	70	63	59	78	69	63	58	68	62	58		66	61	58		65	61	57	56
8	75	65	59	54	74	64	58	54	63	58	54		62	57	53		61	57	53	52
9	71	61	54	50	70	60	54	50	59	54	50		58	53	50		57	53	49	48
10	68	57	51	47	66	57	50	46	56	50	46		55	50	46		54	49	46	45

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	223493
5°	222217
10°	220729
15°	216616
20°	208802
25°	199891
30°	190446
35°	157136
40°	102144
45°	53375
50°	24791
55°	9118
60°	888
65°	700
70°	433
75°	572
80°	0
85°	0



TEST NUMBER: P494367

CATALOG NUMBER: LDA2B059730R70D010 2LBDLC1MMS

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	42.4	7.5
10°-20°	119.2	21.1
20°-30°	169.2	30.0
30°-40°	158.2	28.0
40°-50°	63.6	11.3
50°-60°	11.1	2.0
60°-70°	0.5	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	330.8	58.6
0°-40°	489.0	86.6
0°-60°	563.7	99.9
0°-90°	564.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	564.5	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	453	
5°	449	42
15°	424	119
25°	367	169
35°	261	158
45°	76	64
55°	11	11
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P494367

CATALOG NUMBER: LDA2B059730R70D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	453.0
1°	453.7
2°	452.7
3°	450.9
4°	449.9
5°	448.7
6°	443.7
7°	445.3
8°	440.9
9°	440.0
10°	440.6
11°	436.6
12°	435.6
13°	430.7
14°	428.8
15°	424.1
16°	421.3
17°	415.7
18°	409.2
19°	405.5
20°	397.7
21°	391.8
22.5°	380.9
23°	378.1
24°	372.8
25°	367.2
26°	362.9
27°	356.6
28°	350.4
29°	343.0
30°	334.3
32.5°	303.8
35°	260.9
37.5°	210.2
40°	158.6
42.5°	113.2
45°	76.5
47.5°	50.4
50°	32.3
52.5°	20.2
55°	10.6
57.5°	3.4
60°	0.9
62.5°	0.6
65°	0.6



TEST NUMBER: P494367

CATALOG NUMBER: LDA2B059730R70D010 2LBDLC1MMS

**CANDELA DISTRIBUTION (continued):**

	0°
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.3
77.5°	0.3
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

(END OF REPORT)