

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P314948

Luminaire Tested: **LDA2B05NFL9730D010 PINW1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P314948
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B05NFL9730D010 PINW1MB
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in Adj PinHole, White oculus black finish
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 540.7 lumens
Efficiency: N/A
Efficacy: 77.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P314948

CATALOG NUMBER: LDA2B05NFL9730D010 PINW1MB

Luminous Intensity Polar Plot





TEST NUMBER: P314948

CATALOG NUMBER: LDA2B05NFL9730D010 PINW1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100	100	100	100	100	100	100																
	1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97	97	97	97	97	97	97	97	97																
	2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94	94	94	94	94	94	94	94	94																
	3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91	91	91	91	91	91	91	91	91																
	4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89	89	89	89	89	89	89	89	89																
	5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86	86	86	86	86	86	86	86	86																
	6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84	84	84	84	84	84	84	84	84	84															
	7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82	82	82	82	82	82	82	82	82	82															
	8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80	80	80	80	80	80	80	80	80	80															
	9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78	78	78	78	78	78	78	78	78	78															
	10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76	76	76	76	76	76	76	76	76	76															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1383978
5°	1276398
10°	860120
15°	424089
20°	181134
25°	71203
30°	28029
35°	12287
40°	5925
45°	2861
50°	1535
55°	860
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P314948

CATALOG NUMBER: LDA2B05NFL9730D010 PINW1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	218.3	40.4
10°-20°	235.1	43.5
20°-30°	67.9	12.6
30°-40°	14.3	2.6
40°-50°	3.5	0.7
50°-60°	1.0	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	521.3	96.4
0°-40°	535.7	99.1
0°-60°	540.2	99.9
0°-90°	540.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	540.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2805	
5°	2577	218
15°	830	235
25°	131	68
35°	20	14
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P314948

CATALOG NUMBER: LDA2B05NFL9730D010 PINW1MB

CANDELA DISTRIBUTION (FULL):

	0°
0°	2805.2
1°	2787.7
2°	2757.8
3°	2717.5
4°	2660.4
5°	2577.3
6°	2465.1
7°	2318.7
8°	2138.7
9°	1928.8
10°	1716.9
11°	1502.7
12°	1300.5
13°	1121.0
14°	963.1
15°	830.3
17.5°	548.8
20°	345.0
22.5°	212.2
25°	130.8
27.5°	79.8
30°	49.2
32.5°	31.1
35°	20.4
37.5°	13.5
40°	9.2
42.5°	6.4
45°	4.1
47.5°	2.5
50°	2.0
52.5°	1.5
55°	1.0
57.5°	0.8
60°	0.5
62.5°	0.5
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0



TEST NUMBER: P314948

CATALOG NUMBER: LDA2B05NFL9730D010 PINW1MB

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)