

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P278523

Luminaire Tested: **LDA2B05D2WD010 EU2B05NFL25D2W 2LBALD1H**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P278523
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1811-033-2)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B05D2WD010 EU2B05NFL25D2W 2LBALD1H
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC
AND 2in ADJ spun Refl w/lens Self-Flanged, LI
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 582.1 lumens
Efficiency: N/A
Efficacy: 83.2 lumens/watt
Spacing Criteria (0/90/45): 0.39 / 0.39 / 0.39
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P278523

CATALOG NUMBER: LDA2B05D2WD010 EU2B05NFL25D2W 2LBALD1H

Luminous Intensity Polar Plot





TEST NUMBER: P278523

CATALOG NUMBER: LDA2B05D2WD010 EU2B05NFL25D2W 2LBALD1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	110	113	111	109	108	107	106	105	103	102	102	100	99	99	97	97	97	97
2	112	108	105	103	110	107	104	102	103	101	100	101	99	98	98	97	96	94	94	94	94
3	108	104	100	98	107	103	99	97	100	98	95	98	96	94	96	94	93	91	91	91	91
4	105	100	96	94	104	99	96	93	97	94	92	95	93	91	94	92	90	89	89	89	89
5	102	97	93	90	101	96	92	90	94	91	89	93	90	88	92	89	87	86	86	86	86
6	100	94	90	87	98	93	89	87	92	89	86	91	88	86	89	87	85	84	84	84	84
7	97	91	87	84	96	90	87	84	89	86	84	88	85	83	87	85	83	82	82	82	82
8	95	88	85	82	94	88	84	82	87	84	81	86	83	81	85	83	81	80	80	80	80
9	92	86	82	80	92	86	82	80	85	82	79	84	81	79	84	81	79	78	78	78	78
10	90	84	80	78	90	84	80	78	83	80	77	82	79	77	82	79	77	76	76	76	76

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1489854
5°	1374011
10°	925898
15°	456522
20°	194994
25°	76647
30°	30193
35°	13250
40°	6376
45°	3070
50°	1689
55°	946
60°	493
65°	350
70°	433
75°	0
80°	0
85°	0



TEST NUMBER: P278523

CATALOG NUMBER: LDA2B05D2WD010 EU2B05NFL25D2W 2LBALD1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	235.0	40.4
10°-20°	253.1	43.5
20°-30°	73.1	12.6
30°-40°	15.4	2.7
40°-50°	3.8	0.7
50°-60°	1.1	0.2
60°-70°	0.4	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	561.2	96.4
0°-40°	576.6	99.1
0°-60°	581.5	99.9
0°-90°	582.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	582.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	3020	
5°	2774	235
15°	894	253
25°	141	73
35°	22	15
45°	4	4
55°	1	1
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P278523

CATALOG NUMBER: LDA2B05D2WD010 EU2B05NFL25D2W 2LBALD1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	3019.8
1°	3000.9
2°	2968.8
3°	2925.4
4°	2863.9
5°	2774.4
6°	2653.6
7°	2496.1
8°	2302.3
9°	2076.4
10°	1848.2
11°	1617.7
12°	1400.0
13°	1206.7
14°	1036.8
15°	893.8
17.5°	590.7
20°	371.4
22.5°	228.4
25°	140.8
27.5°	85.9
30°	53.0
32.5°	33.5
35°	22.0
37.5°	14.5
40°	9.9
42.5°	6.9
45°	4.4
47.5°	2.7
50°	2.2
52.5°	1.6
55°	1.1
57.5°	0.8
60°	0.5
62.5°	0.5
65°	0.3
67.5°	0.3
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.3
80°	0.0
82.5°	0.0



TEST NUMBER: P278523

CATALOG NUMBER: LDA2B05D2WD010 EU2B05NFL25D2W 2LBALD1H

CANDELA DISTRIBUTION (continued):

0°
90° | 0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180°







85°		0.0
87.5°		0.0



(END OF REPORT)