

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742909

Luminaire Tested: LD4D15D010-EU4DR1515309030-4LBS1H

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P742909  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D15D010-EU4DR1515309030-4LBS1H  
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1427.6 lumens  
Efficiency: N/A  
Efficacy: 90.4 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P742909  
CATALOG NUMBER: LD4D15D010-EU4DR1515309030-4LBS1H

### Luminous Intensity Polar Plot





TEST NUMBER: P742909

CATALOG NUMBER: LD4D15D010-EU4DR1515309030-4LBS1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2188603	2188603	2188603
5°	1286124	1269477	1279518
10°	383849	386536	392452
15°	95482	97340	94335
20°	28564	33081	29170
25°	10073	12830	10197
30°	3699	4875	3759
35°	1852	2091	1794
40°	1172	1285	1172
45°	868	924	868
50°	688	688	688
55°	571	571	571
60°	463	463	463
65°	350	350	350
70°	300	300	300
75°	189	189	249
80°	126	126	126
85°	66	66	66

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 924 cd/sqm



TEST NUMBER: P742909

CATALOG NUMBER: LD4D15D010-EU4DR1515309030-4LBS1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	925.9	64.9
10°-20°	380.8	26.7
20°-30°	75.6	5.3
30°-40°	18.9	1.3
40°-50°	9.9	0.7
50°-60°	7.4	0.5
60°-70°	5.2	0.4
70°-80°	3.0	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1382.4	96.8
0°-40°	1401.3	98.2
0°-60°	1418.6	99.4
0°-90°	1427.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1427.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	19451	19451	19451	19451	19451	
5°	12655	12525	12491	12578	12590	924
15°	1099	1120	1121	1101	1086	377
25°	129	147	165	146	131	68
35°	26	27	29	27	25	17
45°	12	12	13	12	12	10
55°	8	8	8	8	8	7
65°	5	5	5	5	5	5
75°	2	2	2	2	3	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P742909

CATALOG NUMBER: LD4D15D010-EU4DR1515309030-4LBS1H

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	19450.8	19450.8	19450.8	19450.8	19450.8
2.5°	17545.4	17560.2	17566.0	17583.3	17647.5
5°	12655.1	12525.0	12491.3	12577.7	12590.1
7.5°	7496.4	7522.8	7619.1	7640.5	7563.1
10°	4113.8	4147.6	4142.6	4172.3	4206.0
12.5°	2103.8	2077.5	2069.3	2103.0	2056.1
15°	1099.3	1119.9	1120.7	1100.9	1086.1
17.5°	591.2	615.1	654.6	622.5	573.1
20°	349.1	370.5	404.3	377.9	356.5
22.5°	215.7	233.0	256.9	236.3	219.0
25°	129.3	146.6	164.7	145.7	130.9
27.5°	76.6	91.4	102.9	90.6	75.8
30°	49.4	57.6	65.1	56.8	50.2
32.5°	34.6	37.9	41.2	37.9	34.6
35°	25.5	27.2	28.8	27.2	24.7
37.5°	19.8	21.4	22.2	20.6	18.9
40°	16.5	17.3	18.1	17.3	16.5
42.5°	14.0	14.8	14.8	14.8	14.0
45°	12.4	12.4	13.2	12.4	12.4
47.5°	10.7	10.7	11.5	10.7	10.7
50°	9.9	9.9	9.9	9.9	9.9
52.5°	9.1	9.1	9.1	9.1	9.1
55°	8.2	8.2	8.2	8.2	8.2
57.5°	7.4	7.4	7.4	7.4	7.4
60°	6.6	6.6	6.6	6.6	6.6
62.5°	5.8	5.8	5.8	5.8	5.8
65°	4.9	4.9	4.9	4.9	4.9
67.5°	4.9	4.9	4.9	4.9	4.9
70°	4.1	4.1	4.1	4.1	4.1
72.5°	3.3	3.3	3.3	3.3	3.3
75°	2.5	2.5	2.5	2.5	3.3
77.5°	2.5	2.5	2.5	2.5	2.5
80°	1.6	1.6	1.6	1.6	1.6
82.5°	1.6	1.6	1.6	1.6	1.6
85°	0.8	0.8	0.8	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)