

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742983

Luminaire Tested: LD4D15D010-EU4DR2015309030-4LBDP1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P742983
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR2015309030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1311.5 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P742983
CATALOG NUMBER: LD4D15D010-EU4DR2015309030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P742983

CATALOG NUMBER: LD4D15D010-EU4DR2015309030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	815577
5°	735809
10°	412975
15°	209919
20°	88879
25°	41025
30°	21725
35°	11698
40°	6261
45°	3693
50°	2142
55°	1143
60°	721
65°	517
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3693 cd/sqm



TEST NUMBER: P742983

CATALOG NUMBER: LD4D15D010-EU4DR2015309030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	531.5	40.5
10°-20°	523.3	39.9
20°-30°	171.0	13.0
30°-40°	58.2	4.4
40°-50°	19.6	1.5
50°-60°	5.9	0.5
60°-70°	2.0	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1225.7	93.5
0°-40°	1284.0	97.9
0°-60°	1309.4	99.8
0°-90°	1311.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1311.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7464	
5°	6709	531
15°	1856	523
25°	340	171
35°	88	58
45°	24	20
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P742983

CATALOG NUMBER: LD4D15D010-EU4DR2015309030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	7464.5
0.5°	7464.5
1°	7455.2
1.5°	7436.6
2°	7402.7
2.5°	7357.5
3°	7293.7
3.5°	7204.6
4°	7072.3
4.5°	6911.5
5°	6708.8
5.5°	6442.2
6°	6169.0
6.5°	5856.0
7°	5549.5
7.5°	5190.6
8°	4870.2
8.5°	4547.8
9°	4250.1
9.5°	3976.9
10°	3722.3
12.5°	2672.7
15°	1855.8
17.5°	1212.4
20°	764.4
22.5°	495.2
25°	340.3
27.5°	239.3
30°	172.2
32.5°	123.6
35°	87.7
37.5°	61.2
40°	43.9
42.5°	31.9
45°	23.9
47.5°	18.6
50°	12.6
52.5°	8.0
55°	6.0
57.5°	4.7
60°	3.3
62.5°	2.7
65°	2.0



TEST NUMBER: P742983

CATALOG NUMBER: LD4D15D010-EU4DR2015309030-4LBDP1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.3
70°		0.7

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)