

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743739

Luminaire Tested: LD4D15D010-EU4DR700215IC9030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743739
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1058.8 lumens
Efficiency: N/A
Efficacy: 67.0 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743739

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P743739

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																											
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																											
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																											
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																											
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																											
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																											
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																											
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																											
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																											
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																											
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																											

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	130064
5°	126196
10°	122673
15°	121067
20°	113052
25°	84932
30°	60041
35°	21275
40°	11182
45°	11913
50°	12324
55°	12553
60°	12652
65°	12384
70°	11692
75°	10807
80°	9564
85°	7772

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 12652 cd/sqm



TEST NUMBER: P743739

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.5	10.3
10°-20°	297.7	28.1
20°-30°	327.9	31.0
30°-40°	125.3	11.8
40°-50°	59.2	5.6
50°-60°	58.8	5.6
60°-70°	47.1	4.4
70°-80°	27.1	2.6
80°-90°	7.3	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	734.1	69.3
0°-40°	859.3	81.2
0°-60°	977.3	92.3
0°-90°	1058.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1058.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1190	
5°	1151	109
15°	1070	298
25°	704	328
35°	160	125
45°	77	59
55°	66	59
65°	48	47
75°	26	27
85°	6	7
90°	0	



TEST NUMBER: P743739

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	1190.4
2.5°	1177.9
5°	1150.6
7.5°	1127.8
10°	1105.7
12.5°	1087.1
15°	1070.3
17.5°	1029.8
20°	972.3
22.5°	848.3
25°	704.5
27.5°	613.3
30°	475.9
32.5°	307.4
35°	159.5
37.5°	86.1
40°	78.4
42.5°	77.9
45°	77.1
47.5°	75.4
50°	72.5
52.5°	69.4
55°	65.9
57.5°	62.2
60°	57.9
62.5°	52.9
65°	47.9
67.5°	42.2
70°	36.6
72.5°	30.9
75°	25.6
77.5°	20.2
80°	15.2
82.5°	10.7
85°	6.2
87.5°	2.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)