

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743004

Luminaire Tested: LD4D15D010-EU4DR2015309040-4LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743004
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR2015309040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1323.3 lumens
Efficiency: N/A
Efficacy: 83.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743004
CATALOG NUMBER: LD4D15D010-EU4DR2015309040-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P743004

CATALOG NUMBER: LD4D15D010-EU4DR2015309040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10		0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10
RCR																				
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97		
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94		
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91		
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88		
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85		
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83		
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81		
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79		
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77		
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75		

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	822963
5°	742466
10°	416714
15°	211819
20°	89681
25°	41399
30°	21915
35°	11804
40°	6318
45°	3724
50°	2159
55°	1143
60°	743
65°	517
70°	224
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3724 cd/sqm



TEST NUMBER: P743004

CATALOG NUMBER: LD4D15D010-EU4DR2015309040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	536.3	40.5
10°-20°	528.1	39.9
20°-30°	172.5	13.0
30°-40°	58.7	4.4
40°-50°	19.7	1.5
50°-60°	5.9	0.4
60°-70°	2.0	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1236.8	93.5
0°-40°	1295.6	97.9
0°-60°	1321.3	99.8
0°-90°	1323.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1323.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	7532	
5°	6770	536
15°	1873	528
25°	343	173
35°	88	59
45°	24	20
55°	6	6
65°	2	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743004

CATALOG NUMBER: LD4D15D010-EU4DR2015309040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	7532.1
0.5°	7532.1
1°	7522.7
1.5°	7503.9
2°	7469.7
2.5°	7424.1
3°	7359.7
3.5°	7269.8
4°	7136.4
4.5°	6974.1
5°	6769.5
5.5°	6500.5
6°	6224.9
6.5°	5909.0
7°	5599.8
7.5°	5237.6
8°	4914.3
8.5°	4589.0
9°	4288.5
9.5°	4012.9
10°	3756.0
12.5°	2696.9
15°	1872.6
17.5°	1223.4
20°	771.3
22.5°	499.7
25°	343.4
27.5°	241.5
30°	173.7
32.5°	124.8
35°	88.5
37.5°	61.7
40°	44.3
42.5°	32.2
45°	24.1
47.5°	18.8
50°	12.7
52.5°	8.0
55°	6.0
57.5°	4.7
60°	3.4
62.5°	2.7
65°	2.0



TEST NUMBER: P743004
CATALOG NUMBER: LD4D15D010-EU4DR2015309040-4LBDP1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.3
70°		0.7

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)