

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743613

Luminaire Tested: LD4D15D010-EU4DR600215IC9040-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743613
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR600215IC9040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1323.1 lumens
Efficiency: N/A
Efficacy: 83.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743613
CATALOG NUMBER: LD4D15D010-EU4DR600215IC9040-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P743613

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	171681
5°	175902
10°	178024
15°	169593
20°	149527
25°	120942
30°	81804
35°	40989
40°	6647
45°	6505
50°	6646
55°	6743
60°	6927
65°	7084
70°	7252
75°	7345
80°	7047
85°	5892

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 7345 cd/sqm



TEST NUMBER: P743613

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	153.3	11.6
10°-20°	414.7	31.3
20°-30°	446.2	33.7
30°-40°	193.9	14.7
40°-50°	32.6	2.5
50°-60°	31.7	2.4
60°-70°	27.1	2.0
70°-80°	18.1	1.4
80°-90°	5.4	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1014.2	76.7
0°-40°	1208.1	91.3
0°-60°	1272.4	96.2
0°-90°	1323.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1323.1	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1571	
5°	1604	153
15°	1499	415
25°	1003	446
35°	307	194
45°	42	33
55°	35	32
65°	27	27
75°	17	18
85°	5	5
90°	0	



TEST NUMBER: P743613

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1571.3
2.5°	1615.5
5°	1603.8
7.5°	1607.5
10°	1604.6
12.5°	1571.5
15°	1499.3
17.5°	1402.4
20°	1286.0
22.5°	1161.5
25°	1003.2
27.5°	802.4
30°	648.4
32.5°	499.8
35°	307.3
37.5°	131.5
40°	46.6
42.5°	43.0
45°	42.1
47.5°	40.7
50°	39.1
52.5°	37.2
55°	35.4
57.5°	33.5
60°	31.7
62.5°	29.7
65°	27.4
67.5°	25.2
70°	22.7
72.5°	20.1
75°	17.4
77.5°	14.3
80°	11.2
82.5°	8.0
85°	4.7
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)