

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743758

Luminaire Tested: LD4D15D010-EU4DR700215IC9040-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743758
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9040-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 855.6 lumens
Efficiency: N/A
Efficacy: 54.2 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743758

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9040-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P743758

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9040-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91			91
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83			83
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76			76
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70			70
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65			65
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61			61
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57			57
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53			53
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50			50
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48			48

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105098
5°	101979
10°	99142
15°	97833
20°	91356
25°	68632
30°	48522
35°	17193
40°	9043
45°	9626
50°	9961
55°	10153
60°	10227
65°	10005
70°	9456
75°	8739
80°	7739
85°	6268

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 10227 cd/sqm



TEST NUMBER: P743758

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9040-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	10.3
10°-20°	240.6	28.1
20°-30°	264.9	31.0
30°-40°	101.2	11.8
40°-50°	47.8	5.6
50°-60°	47.5	5.6
60°-70°	38.1	4.4
70°-80°	21.9	2.6
80°-90°	5.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	593.2	69.3
0°-40°	694.4	81.2
0°-60°	789.7	92.3
0°-90°	855.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	855.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	962	
5°	930	88
15°	865	241
25°	569	265
35°	129	101
45°	62	48
55°	53	47
65°	39	38
75°	21	22
85°	5	6
90°	0	



TEST NUMBER: P743758

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9040-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	961.9
2.5°	951.9
5°	929.8
7.5°	911.4
10°	893.6
12.5°	878.4
15°	864.9
17.5°	832.2
20°	785.7
22.5°	685.5
25°	569.3
27.5°	495.6
30°	384.6
32.5°	248.4
35°	128.9
37.5°	69.6
40°	63.4
42.5°	62.9
45°	62.3
47.5°	60.9
50°	58.6
52.5°	56.0
55°	53.3
57.5°	50.2
60°	46.8
62.5°	42.8
65°	38.7
67.5°	34.1
70°	29.6
72.5°	25.0
75°	20.7
77.5°	16.3
80°	12.3
82.5°	8.7
85°	5.0
87.5°	2.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)