

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P283664

Luminaire Tested: **LDA2B159027D010 EU2B15FL409027 2LBAPINSQ1MW**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P283664
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1809-951-15)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B159027D010 EU2B15FL409027 2LBAPINSQ1MW
Description: PORTFOLIO 2IN ADJ 1500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in Adj SQ PinHole, MW

Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 979.4 lumens
Efficiency: N/A
Efficacy: 69.5 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 14.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P283664

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBAPINSQ1MW

Luminous Intensity Polar Plot





TEST NUMBER: P283664

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBAPINSQ1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90																			
3	105	100	96	92	104	99	95	92	96	93	90	94	91	89	92	89	88	86																			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	83	82																			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79																			
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75																			
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72																			
8	87	80	75	71	86	79	75	71	78	74	71	77	73	71	76	73	70	69																			
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67																			
10	82	74	69	66	81	73	69	66	73	69	66	72	68	65	71	68	65	64																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	1290437	1290437	1290437
5°	1234946	1225735	1236878
10°	1052143	1045530	1053245
15°	775496	780552	777998
20°	484125	493051	473415
25°	250081	268317	237506
30°	119919	137408	114279
35°	61915	68480	57940
40°	34714	36453	32910
45°	21071	21071	20304
50°	10976	13509	10976
55°	5677	8946	6107
60°	6512	6512	6512
65°	7004	7004	7004
70°	8655	7934	8655
75°	8387	8387	8387
80°	7671	7671	7671
85°	6227	6227	6227



TEST NUMBER: P283664

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBAPINSQ1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	225.0	23.0
10°-20°	413.3	42.2
20°-30°	224.0	22.9
30°-40°	71.9	7.3
40°-50°	24.5	2.5
50°-60°	8.6	0.9
60°-70°	6.2	0.6
70°-80°	4.6	0.5
80°-90°	1.3	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	862.3	88.0
0°-40°	934.2	95.4
0°-60°	967.3	98.8
0°-90°	979.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	979.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	2616	2616	2616	2616	2616	
5°	2494	2478	2475	2500	2498	225
15°	1518	1531	1528	1535	1523	412
25°	459	480	493	459	436	220
35°	103	107	114	103	96	69
45°	30	31	30	30	29	24
55°	7	8	10	8	7	7
65°	6	7	6	7	6	6
75°	4	4	4	4	4	5
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P283664

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBAPINSQ1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	2615.6	2615.6	2615.6	2615.6	2615.6
1°	2611.2	2592.6	2589.8	2614.0	2608.5
2°	2590.4	2572.8	2570.0	2594.2	2589.3
3°	2567.3	2551.3	2545.9	2571.1	2567.8
4°	2536.5	2521.7	2516.7	2542.0	2539.3
5°	2493.6	2478.3	2475.0	2499.7	2497.5
6°	2440.9	2428.3	2422.2	2446.9	2442.5
7°	2375.0	2363.4	2356.8	2375.0	2377.2
8°	2289.2	2283.7	2276.0	2294.2	2294.2
9°	2198.0	2193.1	2184.8	2201.3	2201.3
10°	2100.2	2096.9	2087.0	2102.4	2102.4
11°	1993.1	1991.4	1984.3	1996.9	1996.9
12°	1880.4	1884.2	1877.7	1888.6	1884.8
13°	1767.8	1766.1	1766.7	1774.9	1768.9
14°	1640.3	1650.2	1651.8	1656.8	1647.4
15°	1518.3	1530.9	1528.2	1535.3	1523.2
16°	1393.5	1407.8	1407.3	1408.9	1397.4
17°	1277.0	1285.3	1285.8	1284.2	1269.9
18°	1152.9	1164.4	1164.4	1161.7	1144.6
19°	1031.4	1040.2	1046.3	1040.2	1020.4
20°	922.1	928.1	939.1	923.7	901.7
21°	817.1	822.6	831.9	813.8	789.6
22°	716.6	723.7	732.5	711.6	686.3
23°	622.6	639.1	642.4	613.8	592.4
24°	536.3	555.0	560.5	531.4	508.8
25°	459.4	480.3	492.9	458.8	436.3
26°	392.9	413.2	428.6	394.5	373.1
27°	334.6	356.1	372.0	340.1	319.8
28°	284.6	305.5	322.0	292.3	273.1
29°	247.3	259.4	275.9	251.1	233.5
30°	210.5	223.6	241.2	216.0	200.6
32.5°	144.5	151.7	165.4	150.0	137.9
35°	102.8	107.2	113.7	103.3	96.2
37.5°	73.1	75.3	79.1	73.1	69.2
40°	53.9	55.0	56.6	53.3	51.1
42.5°	40.1	40.7	40.7	39.6	38.5
45°	30.2	30.8	30.2	30.2	29.1
47.5°	22.0	23.6	23.1	23.1	21.4
50°	14.3	17.6	17.6	17.0	14.3
52.5°	8.8	12.1	13.7	12.1	9.3
55°	6.6	8.2	10.4	8.2	7.1
57.5°	6.6	6.6	7.7	6.6	6.6
60°	6.6	6.6	6.6	6.6	6.6



TEST NUMBER: P283664

CATALOG NUMBER: LDA2B159027D010 EU2B15FL409027 2LBAPINSQ1MW

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
67.5°	6.0	6.0	6.0	6.0	6.0
70°	6.0	6.0	5.5	6.0	6.0
72.5°	5.5	5.5	4.9	5.5	4.9
75°	4.4	4.4	4.4	4.4	4.4
77.5°	3.3	3.3	3.3	3.3	3.3
80°	2.7	2.7	2.7	2.7	2.7
82.5°	1.6	1.6	1.6	2.2	1.6
85°	1.1	1.1	1.1	1.1	1.1
87.5°	0.5	0.5	0.5	0.5	0.5
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - - 90°-270°







62.5°	6.6	6.6	6.6	6.6	6.6
65°	6.0	6.6	6.0	6.6	6.0



(END OF REPORT)