

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743784

Luminaire Tested: LD4D20D010-EU4DR1015209024-4LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743784
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR1015209024-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1521.1 lumens
Efficiency: N/A
Efficacy: 65.8 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743784

CATALOG NUMBER: LD4D20D010-EU4DR1015209024-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P743784

CATALOG NUMBER: LD4D20D010-EU4DR1015209024-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

| | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|-----|----|----|-----|--|--|--|--|--|--|----|--|--|--|--|--|--|--|--|---|
| RF | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | 20 | | | | | | | | | |
| RC | 80 | | | | | | | | | 50 | | | | | | | | | 30 | | | | | | | | | 10 | | | | | | | | | 0 |
| RW | 70 | 50 | 30 | 10 | 70 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 50 | 30 | 10 | 0 | | | | | | | | | | | | | | | | |
| RCR | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | | |
| 0 | 119 | 119 | 119 | 119 | 116 | 116 | 116 | 116 | 111 | 111 | 111 | 106 | 106 | 106 | 102 | 102 | 102 | 100 | | | 100 | | | | | | | | | | | | | | | | |
| 1 | 116 | 114 | 113 | 111 | 114 | 112 | 111 | 109 | 108 | 107 | 106 | 104 | 104 | 103 | 101 | 101 | 100 | 98 | | | 98 | | | | | | | | | | | | | | | | |
| 2 | 113 | 110 | 108 | 106 | 111 | 108 | 106 | 104 | 105 | 104 | 102 | 103 | 101 | 100 | 100 | 99 | 98 | 97 | | | 97 | | | | | | | | | | | | | | | | |
| 3 | 111 | 107 | 104 | 102 | 109 | 106 | 103 | 101 | 103 | 101 | 99 | 101 | 99 | 98 | 99 | 98 | 96 | 95 | | | 95 | | | | | | | | | | | | | | | | |
| 4 | 108 | 104 | 101 | 99 | 107 | 103 | 100 | 98 | 101 | 99 | 97 | 99 | 97 | 96 | 98 | 96 | 95 | 94 | | | 94 | | | | | | | | | | | | | | | | |
| 5 | 106 | 102 | 99 | 96 | 105 | 101 | 98 | 96 | 99 | 97 | 95 | 98 | 96 | 94 | 97 | 95 | 94 | 93 | | | 93 | | | | | | | | | | | | | | | | |
| 6 | 104 | 100 | 96 | 94 | 103 | 99 | 96 | 94 | 98 | 95 | 93 | 97 | 94 | 93 | 96 | 94 | 92 | 91 | | | 91 | | | | | | | | | | | | | | | | |
| 7 | 103 | 98 | 95 | 93 | 102 | 97 | 94 | 92 | 96 | 94 | 92 | 95 | 93 | 92 | 95 | 93 | 91 | 90 | | | 90 | | | | | | | | | | | | | | | | |
| 8 | 101 | 96 | 93 | 91 | 100 | 96 | 93 | 91 | 95 | 92 | 91 | 94 | 92 | 90 | 93 | 92 | 90 | 89 | | | 89 | | | | | | | | | | | | | | | | |
| 9 | 100 | 95 | 92 | 90 | 99 | 94 | 92 | 90 | 94 | 91 | 90 | 93 | 91 | 89 | 93 | 91 | 89 | 88 | | | 88 | | | | | | | | | | | | | | | | |
| 10 | 98 | 94 | 91 | 89 | 98 | 93 | 91 | 89 | 93 | 90 | 88 | 92 | 90 | 88 | 92 | 90 | 88 | 87 | | | 87 | | | | | | | | | | | | | | | | |

AVERAGE LUMINANCE (cd/sqm):

| | |
|-----|---------|
| | 0° |
| 0° | 3618552 |
| 5° | 1715914 |
| 10° | 351910 |
| 15° | 96612 |
| 20° | 38940 |
| 25° | 20868 |
| 30° | 12339 |
| 35° | 8030 |
| 40° | 5363 |
| 45° | 3492 |
| 50° | 1921 |
| 55° | 1429 |
| 60° | 830 |
| 65° | 0 |
| 70° | 0 |
| 75° | 0 |
| 80° | 0 |
| 85° | 0 |

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 3492 cd/sqm



TEST NUMBER: P743784

CATALOG NUMBER: LD4D20D010-EU4DR1015209024-4LBDP1B

ZONAL LUMENS:

| Zone | Lumens | % Fixture |
|-----------|--------|-----------|
| 0°-10° | 1081.6 | 71.1 |
| 10°-20° | 292.7 | 19.2 |
| 20°-30° | 83.8 | 5.5 |
| 30°-40° | 38.3 | 2.5 |
| 40°-50° | 17.6 | 1.2 |
| 50°-60° | 5.8 | 0.4 |
| 60°-70° | 1.4 | 0.1 |
| 70°-80° | 0.0 | 0.0 |
| 80°-90° | 0.0 | 0.0 |
| 90°-100° | 0.0 | 0.0 |
| 100°-110° | 0.0 | 0.0 |
| 110°-120° | 0.0 | 0.0 |
| 120°-130° | 0.0 | 0.0 |
| 130°-140° | 0.0 | 0.0 |
| 140°-150° | 0.0 | 0.0 |
| 150°-160° | 0.0 | 0.0 |
| 160°-170° | 0.0 | 0.0 |
| 170°-180° | 0.0 | 0.0 |
| 0°-30° | 1458.0 | 95.9 |
| 0°-40° | 1496.3 | 98.4 |
| 0°-60° | 1519.7 | 99.9 |
| 0°-90° | 1521.1 | 100.0 |
| 90°-120° | 0.0 | 0.0 |
| 90°-150° | 0.0 | 0.0 |
| 90°-180° | 0.0 | 0.0 |
| 0°-180° | 1521.1 | 100.0 |

CANDELA DISTRIBUTION:

| | 0° | Flux |
|-----|-------|------|
| 0° | 33118 | |
| 5° | 15645 | ### |
| 15° | 854 | 293 |
| 25° | 173 | 84 |
| 35° | 60 | 38 |
| 45° | 23 | 18 |
| 55° | 8 | 6 |
| 65° | 0 | 1 |
| 75° | 0 | 0 |
| 85° | 0 | 0 |
| 90° | 0 | |



TEST NUMBER: P743784

CATALOG NUMBER: LD4D20D010-EU4DR1015209024-4LBDP1B

CANDELA DISTRIBUTION (FULL):

| | 0° |
|-------|---------|
| 0° | 33118.5 |
| 0.5° | 32832.6 |
| 1° | 32098.9 |
| 1.5° | 30684.1 |
| 2° | 29100.1 |
| 2.5° | 27008.1 |
| 3° | 24682.8 |
| 3.5° | 22432.7 |
| 4° | 20005.8 |
| 4.5° | 17770.8 |
| 5° | 15645.0 |
| 5.5° | 13718.5 |
| 6° | 11882.3 |
| 6.5° | 10268.2 |
| 7° | 8748.1 |
| 7.5° | 7450.0 |
| 8° | 6298.6 |
| 8.5° | 5290.2 |
| 9° | 4417.3 |
| 9.5° | 3751.3 |
| 10° | 3171.9 |
| 12.5° | 1512.6 |
| 15° | 854.1 |
| 17.5° | 519.2 |
| 20° | 334.9 |
| 22.5° | 233.3 |
| 25° | 173.1 |
| 27.5° | 127.9 |
| 30° | 97.8 |
| 32.5° | 75.3 |
| 35° | 60.2 |
| 37.5° | 45.2 |
| 40° | 37.6 |
| 42.5° | 30.1 |
| 45° | 22.6 |
| 47.5° | 15.1 |
| 50° | 11.3 |
| 52.5° | 7.5 |
| 55° | 7.5 |
| 57.5° | 3.8 |
| 60° | 3.8 |
| 62.5° | 3.8 |
| 65° | 0.0 |



TEST NUMBER: P743784
CATALOG NUMBER: LD4D20D010-EU4DR1015209024-4LBDP1B

CANDELA DISTRIBUTION (continued):

| | 0° |
|-------|-----|
| 72.5° | 0.0 |
| 75° | 0.0 |
| 77.5° | 0.0 |
| 80° | 0.0 |
| 82.5° | 0.0 |
| 85° | 0.0 |
| 87.5° | 0.0 |
| 90° | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



| | | |
|-------|--|-----|
| 67.5° | | 0.0 |
| 70° | | 0.0 |

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)