

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743945

Luminaire Tested: LD4D20D010-EU4DR2015309024-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743945
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR2015309024-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1794.5 lumens
Efficiency: N/A
Efficacy: 77.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743945
CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P743945

CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1115946
5°	1006790
10°	565072
15°	287233
20°	121610
25°	56143
30°	29724
35°	16019
40°	8558
45°	5053
50°	2941
55°	1562
60°	983
65°	698
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5053 cd/sqm



TEST NUMBER: P743945

CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	727.2	40.5
10°-20°	716.1	39.9
20°-30°	233.9	13.0
30°-40°	79.7	4.4
40°-50°	26.8	1.5
50°-60°	8.1	0.4
60°-70°	2.7	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1677.2	93.5
0°-40°	1756.8	97.9
0°-60°	1791.7	99.8
0°-90°	1794.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1794.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	10214	
5°	9180	727
15°	2539	716
25°	466	234
35°	120	80
45°	33	27
55°	8	8
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743945
CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	10213.6
0.5°	10213.6
1°	10200.9
1.5°	10175.4
2°	10129.0
2.5°	10067.2
3°	9979.9
3.5°	9858.0
4°	9677.0
4.5°	9456.9
5°	9179.5
5.5°	8814.8
6°	8441.0
6.5°	8012.6
7°	7593.4
7.5°	7102.2
8°	6663.8
8.5°	6222.7
9°	5815.3
9.5°	5441.5
10°	5093.2
12.5°	3657.1
15°	2539.3
17.5°	1658.9
20°	1045.9
22.5°	677.6
25°	465.7
27.5°	327.4
30°	235.6
32.5°	169.2
35°	120.1
37.5°	83.7
40°	60.0
42.5°	43.7
45°	32.7
47.5°	25.5
50°	17.3
52.5°	10.9
55°	8.2
57.5°	6.4
60°	4.5
62.5°	3.6
65°	2.7



TEST NUMBER: P743945
CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1H

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.8
70°		0.9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)