

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744566

Luminaire Tested: LD4D20D010-EU4DR6020359024-4LBDP1LI

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744566  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D20D010-EU4DR6020359024-4LBDP1LI  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1693.9 lumens  
Efficiency: N/A  
Efficacy: 73.3 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744566  
CATALOG NUMBER: LD4D20D010-EU4DR6020359024-4LBDP1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P744566

CATALOG NUMBER: LD4D20D010-EU4DR6020359024-4LBDP1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93			93																
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86			86																
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80			80																
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75			75																
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70			70																
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66			66																
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62			62																
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59			59																
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55			55																
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53			53																

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	219811
5°	225213
10°	227939
15°	217136
20°	191443
25°	154842
30°	104741
35°	52486
40°	8515
45°	8329
50°	8499
55°	8629
60°	8872
65°	9075
70°	9264
75°	9372
80°	9061
85°	7522

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 9372 cd/sqm



TEST NUMBER: P744566

CATALOG NUMBER: LD4D20D010-EU4DR6020359024-4LBDP1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	196.3	11.6
10°-20°	531.0	31.3
20°-30°	571.3	33.7
30°-40°	248.3	14.7
40°-50°	41.7	2.5
50°-60°	40.6	2.4
60°-70°	34.7	2.0
70°-80°	23.2	1.4
80°-90°	6.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1298.5	76.7
0°-40°	1546.8	91.3
0°-60°	1629.1	96.2
0°-90°	1693.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1693.9	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	2012	
5°	2053	196
15°	1920	531
25°	1284	571
35°	394	248
45°	54	42
55°	45	41
65°	35	35
75°	22	23
85°	6	7
90°	0	



TEST NUMBER: P744566  
CATALOG NUMBER: LD4D20D010-EU4DR6020359024-4LBDP1LI

**CANDELA DISTRIBUTION (FULL):**

0°	
0°	2011.8
2.5°	2068.4
5°	2053.4
7.5°	2058.2
10°	2054.5
12.5°	2012.0
15°	1919.6
17.5°	1795.5
20°	1646.5
22.5°	1487.1
25°	1284.4
27.5°	1027.4
30°	830.2
32.5°	639.9
35°	393.5
37.5°	168.3
40°	59.7
42.5°	55.0
45°	53.9
47.5°	52.1
50°	50.0
52.5°	47.7
55°	45.3
57.5°	42.9
60°	40.6
62.5°	38.0
65°	35.1
67.5°	32.2
70°	29.0
72.5°	25.7
75°	22.2
77.5°	18.3
80°	14.4
82.5°	10.2
85°	6.0
87.5°	2.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)