

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743804

Luminaire Tested: LD4D20D010-EU4DR1015209027-4LBS1MW

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743804
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-4)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR1015209027-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 10° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1767.8 lumens
Efficiency: N/A
Efficacy: 76.5 lumens/watt
Spacing Criteria (0/90/45): 0.17 / 0.17 / 0.18
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743804
CATALOG NUMBER: LD4D20D010-EU4DR1015209027-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P743804

CATALOG NUMBER: LD4D20D010-EU4DR1015209027-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	116	114	113	111	114	112	111	109	108	107	106	104	104	103	101	101	100	98				98															
2	113	110	108	106	111	108	106	104	105	104	102	103	101	100	100	99	98	97				97															
3	111	107	104	102	109	106	103	101	103	101	99	101	99	98	99	98	96	95				95															
4	108	104	101	99	107	103	100	98	101	99	97	99	97	96	98	96	95	94				94															
5	106	102	99	96	105	101	98	96	99	97	95	98	96	94	97	95	94	93				93															
6	104	100	96	94	103	99	96	94	98	95	93	97	94	93	96	94	92	91				91															
7	103	98	95	93	102	97	94	92	96	94	92	95	93	92	95	93	91	90				90															
8	101	96	93	91	100	96	93	91	95	92	91	94	92	90	93	92	90	89				89															
9	100	95	92	90	99	94	92	90	94	91	90	93	91	89	93	91	89	88				88															
10	98	94	91	89	98	93	91	89	93	90	88	92	90	88	92	90	88	87				87															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	4205610
5°	1994288
10°	409003
15°	112289
20°	45253
25°	24256
30°	14345
35°	9337
40°	6233
45°	4048
50°	2227
55°	1657
60°	961
65°	0
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4048 cd/sqm



TEST NUMBER: P743804

CATALOG NUMBER: LD4D20D010-EU4DR1015209027-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1257.0	71.1
10°-20°	340.2	19.2
20°-30°	97.4	5.5
30°-40°	44.5	2.5
40°-50°	20.4	1.2
50°-60°	6.8	0.4
60°-70°	1.6	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1694.6	95.9
0°-40°	1739.1	98.4
0°-60°	1766.2	99.9
0°-90°	1767.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1767.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	38492	
5°	18183	###
15°	993	340
25°	201	97
35°	70	44
45°	26	20
55°	9	7
65°	0	2
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743804

CATALOG NUMBER: LD4D20D010-EU4DR1015209027-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	38491.5
0.5°	38159.1
1°	37306.4
1.5°	35662.1
2°	33821.1
2.5°	31389.7
3°	28687.1
3.5°	26072.1
4°	23251.4
4.5°	20653.9
5°	18183.1
5.5°	15944.1
6°	13810.1
6.5°	11934.0
7°	10167.3
7.5°	8658.6
8°	7320.5
8.5°	6148.5
9°	5133.9
9.5°	4359.9
10°	3686.5
12.5°	1758.0
15°	992.7
17.5°	603.5
20°	389.2
22.5°	271.1
25°	201.2
27.5°	148.7
30°	113.7
32.5°	87.5
35°	70.0
37.5°	52.5
40°	43.7
42.5°	35.0
45°	26.2
47.5°	17.5
50°	13.1
52.5°	8.7
55°	8.7
57.5°	4.4
60°	4.4
62.5°	4.4
65°	0.0



TEST NUMBER: P743804

CATALOG NUMBER: LD4D20D010-EU4DR1015209027-4LBS1MW

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		0.0
70°		0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)