

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743877

Luminaire Tested: LD4D20D010-EU4DR1515309027-4LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743877
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR1515309027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 15° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1893.8 lumens
Efficiency: N/A
Efficacy: 82.0 lumens/watt
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743877
CATALOG NUMBER: LD4D20D010-EU4DR1515309027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P743877

CATALOG NUMBER: LD4D20D010-EU4DR1515309027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98																			
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96																			
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94																			
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93																			
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92																			
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90																			
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89																			
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88																			
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87																			
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2903251	2903251	2903251
5°	1706095	1684001	1697325
10°	509189	512753	520600
15°	126655	129121	125135
20°	37892	43882	38702
25°	13360	17021	13531
30°	4905	6462	4987
35°	2462	2774	2382
40°	1548	1704	1548
45°	1148	1225	1148
50°	911	911	911
55°	759	759	759
60°	611	611	611
65°	471	471	471
70°	402	402	402
75°	249	249	333
80°	173	173	173
85°	91	91	91

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 45°
 Vertical Angle: 45°
 Luminance: 1225 cd/sqm



TEST NUMBER: P743877

CATALOG NUMBER: LD4D20D010-EU4DR1515309027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1228.2	64.9
10°-20°	505.2	26.7
20°-30°	100.3	5.3
30°-40°	25.0	1.3
40°-50°	13.2	0.7
50°-60°	9.7	0.5
60°-70°	6.9	0.4
70°-80°	4.0	0.2
80°-90°	1.2	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1833.8	96.8
0°-40°	1858.8	98.2
0°-60°	1881.7	99.4
0°-90°	1893.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1893.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	25802	25802	25802	25802	25802	
5°	16788	16615	16570	16685	16701	1226
15°	1458	1486	1487	1460	1441	500
25°	172	194	218	193	174	90
35°	34	36	38	36	33	23
45°	16	16	18	16	16	13
55°	11	11	11	11	11	10
65°	7	7	7	7	7	7
75°	3	3	3	3	4	4
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P743877

CATALOG NUMBER: LD4D20D010-EU4DR1515309027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	25802.1	25802.1	25802.1	25802.1	25802.1
2.5°	23274.6	23294.2	23301.9	23324.8	23410.0
5°	16787.5	16614.9	16570.1	16684.8	16701.2
7.5°	9944.2	9979.2	10107.0	10135.4	10032.7
10°	5457.1	5501.9	5495.3	5534.6	5579.4
12.5°	2790.8	2755.9	2744.9	2789.7	2727.5
15°	1458.2	1485.5	1486.6	1460.4	1440.7
17.5°	784.3	815.9	868.4	825.8	760.2
20°	463.1	491.5	536.3	501.4	473.0
22.5°	286.2	309.1	340.8	313.5	290.5
25°	171.5	194.4	218.5	193.3	173.7
27.5°	101.6	121.2	136.5	120.2	100.5
30°	65.5	76.5	86.3	75.4	66.6
32.5°	45.9	50.2	54.6	50.2	45.9
35°	33.9	36.0	38.2	36.0	32.8
37.5°	26.2	28.4	29.5	27.3	25.1
40°	21.8	22.9	24.0	22.9	21.8
42.5°	18.6	19.7	19.7	19.7	18.6
45°	16.4	16.4	17.5	16.4	16.4
47.5°	14.2	14.2	15.3	14.2	14.2
50°	13.1	13.1	13.1	13.1	13.1
52.5°	12.0	12.0	12.0	12.0	12.0
55°	10.9	10.9	10.9	10.9	10.9
57.5°	9.8	9.8	9.8	9.8	9.8
60°	8.7	8.7	8.7	8.7	8.7
62.5°	7.6	7.6	7.6	7.6	7.6
65°	6.6	6.6	6.6	6.6	6.6
67.5°	6.6	6.6	6.6	6.6	6.6
70°	5.5	5.5	5.5	5.5	5.5
72.5°	4.4	4.4	4.4	4.4	4.4
75°	3.3	3.3	3.3	3.3	4.4
77.5°	3.3	3.3	3.3	3.3	3.3
80°	2.2	2.2	2.2	2.2	2.2
82.5°	2.2	2.2	2.2	2.2	2.2
85°	1.1	1.1	1.1	1.1	1.1
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)