

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P282117

Luminaire Tested: **LDA2B058027D010 EU2B05NFL258027 2LBAPINSQ1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P282117
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1809-951-26)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B058027D010 EU2B05NFL258027 2LBAPINSQ1MB
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH NARROW FLOOD OPTIC AND 2in Adj SQ PinHole, MB
Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 708.8 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 0.33 / 0.3 / 0.32
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P282117

CATALOG NUMBER: LDA2B058027D010 EU2B05NFL258027 2LBAPINSQ1MB

Luminous Intensity Polar Plot





TEST NUMBER: P282117

CATALOG NUMBER: LDA2B058027D010 EU2B05NFL258027 2LBAPINSQ1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	115	113	112	110	113	111	110	108	107	106	105	104	103	102	100	100	99	97				97															
2	112	109	106	104	110	107	105	103	104	102	100	101	100	98	99	97	96	95				95															
3	109	105	101	99	107	103	100	98	101	99	97	99	97	95	97	95	94	92				92															
4	106	101	98	95	105	100	97	94	98	96	93	96	94	92	95	93	91	90				90															
5	103	98	94	92	102	97	94	91	96	93	91	94	92	90	93	91	89	88				88															
6	101	95	92	89	100	95	91	89	93	90	88	92	90	88	91	89	87	86				86															
7	99	93	89	87	98	92	89	86	91	88	86	90	88	86	89	87	85	84				84															
8	96	91	87	85	96	90	87	84	89	86	84	88	86	84	88	85	83	83				83															
9	94	89	85	83	94	88	85	82	87	84	82	87	84	82	86	84	82	81				81															
10	93	87	83	81	92	86	83	81	86	83	81	85	82	80	85	82	80	79				79															

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	2585808	2585808	2585808
5°	2151647	2112226	2069585
10°	1232443	1156495	1079346
15°	548154	486862	408000
20°	198879	186961	148162
25°	76374	71312	61404
30°	32928	30649	27174
35°	15599	15599	12889
40°	7793	8050	6505
45°	4535	4256	3977
50°	3070	2763	2763
55°	2408	1720	2064
60°	1973	1184	1579
65°	1401	934	1401
70°	1154	577	1154
75°	762	762	762
80°	0	0	0
85°	0	0	0



TEST NUMBER: P282117

CATALOG NUMBER: LDA2B058027D010 EU2B05NFL258027 2LBAPINSQ1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	340.9	48.1
10°-20°	275.9	38.9
20°-30°	66.5	9.4
30°-40°	17.0	2.4
40°-50°	5.1	0.7
50°-60°	2.1	0.3
60°-70°	1.0	0.1
70°-80°	0.3	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	683.3	96.4
0°-40°	700.2	98.8
0°-60°	707.4	99.8
0°-90°	708.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	708.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	5241	5241	5241	5241	5241	
5°	4345	4305	4265	4228	4179	351
15°	1073	1048	953	859	799	306
25°	140	141	131	119	113	72
35°	26	26	26	23	21	18
45°	6	6	6	6	6	5
55°	3	2	2	2	2	2
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	0



TEST NUMBER: P282117

CATALOG NUMBER: LDA2B058027D010 EU2B05NFL258027 2LBAPINSQ1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	5241.2	5241.2	5241.2	5241.2	5241.2
1°	5217.8	5181.4	5176.9	5199.6	5132.9
2°	5084.4	5058.5	5043.5	5056.9	4981.3
3°	4901.3	4876.2	4849.1	4849.5	4765.0
4°	4651.8	4632.0	4586.4	4572.6	4523.7
5°	4344.6	4304.6	4265.0	4227.8	4178.9
6°	4005.1	3953.3	3896.7	3841.4	3791.2
7°	3605.7	3571.3	3496.6	3421.0	3378.5
8°	3230.2	3174.8	3087.5	2992.9	2956.9
9°	2826.4	2786.7	2686.5	2576.5	2540.6
10°	2460.1	2418.9	2308.5	2186.1	2154.5
11°	2116.5	2077.7	1962.9	1834.4	1800.8
12°	1825.9	1770.9	1639.1	1527.6	1494.8
13°	1536.5	1498.9	1374.0	1263.6	1200.2
14°	1290.3	1259.2	1146.0	1049.0	981.9
15°	1073.2	1047.8	953.2	858.6	798.8
16°	880.4	864.6	789.9	698.5	649.6
17°	714.3	699.7	652.0	567.9	526.7
18°	576.8	574.8	535.2	462.4	425.7
19°	474.6	473.8	437.4	376.3	346.0
20°	378.8	384.0	356.1	302.8	282.2
21°	308.8	311.7	289.4	249.0	230.4
22°	251.4	253.5	238.9	205.8	195.6
23°	206.2	207.4	195.2	170.6	161.7
24°	169.8	170.6	159.7	142.3	134.6
25°	140.3	141.1	131.0	118.8	112.8
26°	116.4	117.2	108.3	99.8	93.8
27°	96.6	98.2	89.3	84.1	77.6
28°	82.5	82.9	74.8	71.5	65.5
29°	67.5	69.9	63.1	60.2	55.8
30°	57.8	59.0	53.8	51.7	47.7
32.5°	38.4	39.2	36.8	35.2	31.9
35°	25.9	26.3	25.9	23.4	21.4
37.5°	17.8	17.8	18.2	15.4	14.6
40°	12.1	12.1	12.5	10.5	10.1
42.5°	8.9	8.9	8.5	7.3	7.3
45°	6.5	6.5	6.1	5.7	5.7
47.5°	5.3	4.9	4.4	4.4	4.4
50°	4.0	4.0	3.6	3.2	3.6
52.5°	3.2	3.2	2.8	2.8	2.8
55°	2.8	2.4	2.0	2.0	2.4
57.5°	2.0	2.0	1.6	1.6	2.0
60°	2.0	1.6	1.2	1.6	1.6



TEST NUMBER: P282117

CATALOG NUMBER: LDA2B058027D010 EU2B05NFL258027 2LBAPINSQ1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
67.5°	1.2	0.8	0.8	0.8	0.8
70°	0.8	0.8	0.4	0.4	0.8
72.5°	0.4	0.4	0.4	0.4	0.4
75°	0.4	0.4	0.4	0.4	0.4
77.5°	0.4	0.4	0.0	0.0	0.4
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - - 90°-270°







62.5°	1.6	1.2	1.2	1.2	1.2
65°	1.2	1.2	0.8	0.8	1.2



(END OF REPORT)