

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743968

Luminaire Tested: LD4D20D010-EU4DR2015309030-4LBDP1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743968
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR2015309030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2051.7 lumens
Efficiency: N/A
Efficacy: 88.8 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743968
CATALOG NUMBER: LD4D20D010-EU4DR2015309030-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P743968

CATALOG NUMBER: LD4D20D010-EU4DR2015309030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	89																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	86																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	84																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	82																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	80																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	78																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1275925
5°	1151116
10°	646073
15°	328407
20°	139051
25°	64184
30°	33976
35°	18313
40°	9784
45°	5779
50°	3366
55°	1791
60°	1136
65°	801
70°	319
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 5779 cd/sqm



TEST NUMBER: P743968

CATALOG NUMBER: LD4D20D010-EU4DR2015309030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	831.4	40.5
10°-20°	818.7	39.9
20°-30°	267.5	13.0
30°-40°	91.1	4.4
40°-50°	30.6	1.5
50°-60°	9.2	0.5
60°-70°	3.1	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1917.6	93.5
0°-40°	2008.7	97.9
0°-60°	2048.5	99.8
0°-90°	2051.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2051.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	11678	
5°	10495	831
15°	2903	819
25°	532	267
35°	137	91
45°	37	31
55°	9	9
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743968

CATALOG NUMBER: LD4D20D010-EU4DR2015309030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	11677.8
0.5°	11677.8
1°	11663.2
1.5°	11634.1
2°	11581.1
2.5°	11510.3
3°	11410.5
3.5°	11271.2
4°	11064.2
4.5°	10812.6
5°	10495.4
5.5°	10078.4
6°	9651.1
6.5°	9161.3
7°	8681.9
7.5°	8120.4
8°	7619.1
8.5°	7114.8
9°	6648.9
9.5°	6221.6
10°	5823.3
12.5°	4181.3
15°	2903.3
17.5°	1896.7
20°	1195.9
22.5°	774.7
25°	532.4
27.5°	374.4
30°	269.3
32.5°	193.4
35°	137.3
37.5°	95.7
40°	68.6
42.5°	49.9
45°	37.4
47.5°	29.1
50°	19.8
52.5°	12.5
55°	9.4
57.5°	7.3
60°	5.2
62.5°	4.2
65°	3.1



TEST NUMBER: P743968
CATALOG NUMBER: LD4D20D010-EU4DR2015309030-4LBDP1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.1
70°		1.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)