

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744590

Luminaire Tested: LD4D20D010-EU4DR6020359030-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P744590
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR6020359030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1456.3 lumens
Efficiency: N/A
Efficacy: 63.0 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744590
CATALOG NUMBER: LD4D20D010-EU4DR6020359030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P744590

CATALOG NUMBER: LD4D20D010-EU4DR6020359030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93				93															
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86				86															
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80				80															
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75				75															
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70				70															
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66				66															
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62				62															
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59				59															
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55				55															
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53				53															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	188956
5°	193604
10°	195942
15°	186662
20°	164573
25°	133118
30°	90043
35°	45123
40°	7317
45°	7170
50°	7309
55°	7429
60°	7626
65°	7782
70°	7986
75°	8063
80°	7802
85°	6519

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 8063 cd/sqm



TEST NUMBER: P744590

CATALOG NUMBER: LD4D20D010-EU4DR6020359030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	168.7	11.6
10°-20°	456.4	31.3
20°-30°	491.1	33.7
30°-40°	213.5	14.7
40°-50°	35.9	2.5
50°-60°	34.9	2.4
60°-70°	29.8	2.0
70°-80°	20.0	1.4
80°-90°	6.0	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1116.3	76.7
0°-40°	1329.7	91.3
0°-60°	1400.5	96.2
0°-90°	1456.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1456.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1729	
5°	1765	169
15°	1650	456
25°	1104	491
35°	338	213
45°	46	36
55°	39	35
65°	30	30
75°	19	20
85°	5	6
90°	0	



TEST NUMBER: P744590

CATALOG NUMBER: LD4D20D010-EU4DR6020359030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1729.4
2.5°	1778.0
5°	1765.2
7.5°	1769.3
10°	1766.1
12.5°	1729.6
15°	1650.2
17.5°	1543.5
20°	1415.4
22.5°	1278.4
25°	1104.2
27.5°	883.1
30°	713.7
32.5°	550.1
35°	338.3
37.5°	144.7
40°	51.3
42.5°	47.3
45°	46.4
47.5°	44.8
50°	43.0
52.5°	41.0
55°	39.0
57.5°	36.9
60°	34.9
62.5°	32.7
65°	30.1
67.5°	27.7
70°	25.0
72.5°	22.1
75°	19.1
77.5°	15.8
80°	12.4
82.5°	8.8
85°	5.2
87.5°	1.8
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)