

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744593

Luminaire Tested: LD4D20D010-EU4DR6020359030-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P744593
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR6020359030-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1674.7 lumens
Efficiency: N/A
Efficacy: 72.5 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.84
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744593

CATALOG NUMBER: LD4D20D010-EU4DR6020359030-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P744593

CATALOG NUMBER: LD4D20D010-EU4DR6020359030-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	217298
5°	222647
10°	225343
15°	214658
20°	189269
25°	153082
30°	103555
35°	51886
40°	8415
45°	8236
50°	8397
55°	8534
60°	8763
65°	8971
70°	9168
75°	9287
80°	8935
85°	7522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 9287 cd/sqm



TEST NUMBER: P744593

CATALOG NUMBER: LD4D20D010-EU4DR6020359030-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.0	11.6
10°-20°	524.9	31.3
20°-30°	564.8	33.7
30°-40°	245.5	14.7
40°-50°	41.2	2.5
50°-60°	40.1	2.4
60°-70°	34.3	2.0
70°-80°	22.9	1.4
80°-90°	6.9	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1283.7	76.7
0°-40°	1529.2	91.3
0°-60°	1610.6	96.2
0°-90°	1674.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1674.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1989	
5°	2030	194
15°	1898	525
25°	1270	565
35°	389	245
45°	53	41
55°	45	40
65°	35	34
75°	22	23
85°	6	7
90°	0	



TEST NUMBER: P744593

CATALOG NUMBER: LD4D20D010-EU4DR6020359030-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1988.8
2.5°	2044.7
5°	2030.0
7.5°	2034.7
10°	2031.1
12.5°	1989.1
15°	1897.7
17.5°	1775.1
20°	1627.8
22.5°	1470.1
25°	1269.8
27.5°	1015.7
30°	820.8
32.5°	632.6
35°	389.0
37.5°	166.4
40°	59.0
42.5°	54.4
45°	53.3
47.5°	51.5
50°	49.4
52.5°	47.1
55°	44.8
57.5°	42.5
60°	40.1
62.5°	37.5
65°	34.7
67.5°	31.9
70°	28.7
72.5°	25.4
75°	22.0
77.5°	18.1
80°	14.2
82.5°	10.1
85°	6.0
87.5°	2.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)