

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744370

Luminaire Tested: LD4D20D010-EU4DR4520359035-4LBDP1H

Issue Date: 1/30/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744370  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 1/30/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D20D010-EU4DR4520359035-4LBDP1H  
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 45° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1993.8 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.75 / 0.75 / 0.69  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744370  
CATALOG NUMBER: LD4D20D010-EU4DR4520359035-4LBDP1H

### Luminous Intensity Polar Plot





TEST NUMBER: P744370

CATALOG NUMBER: LD4D20D010-EU4DR4520359035-4LBDP1H

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100		
	1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	98	98	97	95	95	95	95	95	95		
	2	109	105	102	99	107	103	100	98	100	98	95	97	95	93	95	93	91	90	90	90	90	90	90		
	3	105	99	95	91	103	98	94	91	95	92	89	93	90	88	91	89	87	85	85	85	85	85	85		
	4	100	94	89	85	99	93	88	85	91	87	84	89	86	83	87	84	82	81	81	81	81	81	81		
	5	96	89	84	80	95	88	83	80	86	82	79	85	81	79	83	80	78	77	77	77	77	77	77		
	6	92	85	80	76	91	84	79	76	83	78	75	81	77	75	80	77	74	73	73	73	73	73	73		
	7	89	81	75	72	87	80	75	72	79	74	71	78	74	71	77	73	71	69	69	69	69	69	69		
	8	85	77	72	68	84	76	71	68	75	71	68	74	70	67	73	70	67	66	66	66	66	66	66		
	9	82	73	68	65	81	73	68	65	72	68	65	71	67	64	71	67	64	63	63	63	63	63	63		
	10	79	70	65	62	78	70	65	62	69	65	62	68	64	61	68	64	61	60	60	60	60	60	60		

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	385035
5°	374068
10°	357891
15°	327536
20°	259858
25°	162232
30°	89412
35°	40148
40°	15818
45°	7448
50°	3536
55°	1848
60°	918
65°	233
70°	96
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7448 cd/sqm



TEST NUMBER: P744370

CATALOG NUMBER: LD4D20D010-EU4DR4520359035-4LBDP1H

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	320.5	16.1
10°-20°	788.7	39.6
20°-30°	624.6	31.3
30°-40°	208.0	10.4
40°-50°	41.3	2.1
50°-60°	9.4	0.5
60°-70°	1.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1733.7	87.0
0°-40°	1941.7	97.4
0°-60°	1992.4	99.9
0°-90°	1993.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1993.8	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	3524	
5°	3411	320
15°	2896	789
25°	1346	625
35°	301	208
45°	48	41
55°	10	9
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744370

CATALOG NUMBER: LD4D20D010-EU4DR4520359035-4LBDP1H

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	3524.0
2.5°	3501.0
5°	3410.6
7.5°	3336.1
10°	3225.8
12.5°	3078.9
15°	2895.6
17.5°	2620.1
20°	2234.9
22.5°	1775.9
25°	1345.7
27.5°	985.4
30°	708.7
32.5°	482.0
35°	301.0
37.5°	178.5
40°	110.9
42.5°	72.9
45°	48.2
47.5°	31.1
50°	20.8
52.5°	13.9
55°	9.7
57.5°	6.4
60°	4.2
62.5°	2.2
65°	0.9
67.5°	0.3
70°	0.3
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)