

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744774

Luminaire Tested: LD4D20D010-EU4DR7020359040-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P744774
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR7020359040-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2120.3 lumens
Efficiency: N/A
Efficacy: 91.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744774
CATALOG NUMBER: LD4D20D010-EU4DR7020359040-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P744774

CATALOG NUMBER: LD4D20D010-EU4DR7020359040-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	260456
5°	252709
10°	245668
15°	242451
20°	226395
25°	170080
30°	120234
35°	42589
40°	22393
45°	23858
50°	24698
55°	25164
60°	25327
65°	24793
70°	23384
75°	21656
80°	19254
85°	15545

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 25338 cd/sqm



TEST NUMBER: P744774

CATALOG NUMBER: LD4D20D010-EU4DR7020359040-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	217.3	10.2
10°-20°	596.1	28.1
20°-30°	656.5	31.0
30°-40°	250.9	11.8
40°-50°	118.5	5.6
50°-60°	117.8	5.6
60°-70°	94.3	4.4
70°-80°	54.2	2.6
80°-90°	14.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1470.0	69.3
0°-40°	1720.9	81.2
0°-60°	1957.1	92.3
0°-90°	2120.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2120.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2384	
5°	2304	217
15°	2143	596
25°	1411	657
35°	319	251
45°	154	118
55°	132	118
65°	96	94
75°	51	54
85°	12	15
90°	0	



TEST NUMBER: P744774

CATALOG NUMBER: LD4D20D010-EU4DR7020359040-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2383.8
2.5°	2358.8
5°	2304.1
7.5°	2258.5
10°	2214.3
12.5°	2176.9
15°	2143.4
17.5°	2062.2
20°	1947.1
22.5°	1698.7
25°	1410.8
27.5°	1228.1
30°	953.0
32.5°	615.6
35°	319.3
37.5°	172.5
40°	157.0
42.5°	155.9
45°	154.4
47.5°	151.0
50°	145.3
52.5°	138.9
55°	132.1
57.5°	124.6
60°	115.9
62.5°	106.1
65°	95.9
67.5°	84.6
70°	73.2
72.5°	61.9
75°	51.3
77.5°	40.4
80°	30.6
82.5°	21.5
85°	12.4
87.5°	4.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)