

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744707

Luminaire Tested: LD4D20D010-EU4DR6520359050-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744707  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-59)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D20D010-EU4DR6520359050-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 65° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1290.3 lumens  
Efficiency: N/A  
Efficacy: 55.9 lumens/watt  
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 23.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744707  
CATALOG NUMBER: LD4D20D010-EU4DR6520359050-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P744707

CATALOG NUMBER: LD4D20D010-EU4DR6520359050-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	111	108	106	111	108	106	104	104	103	101	101	99	98	97	96	95	93																			
2	108	103	99	95	106	101	97	94	98	95	92	95	92	90	92	90	88	87																			
3	102	96	91	87	100	94	90	86	92	88	85	89	86	83	87	84	82	80																			
4	97	89	84	79	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	83	78	73	90	83	77	73	81	76	72	79	75	72	77	74	71	69																			
6	87	78	72	68	86	77	72	68	76	71	67	74	70	67	73	69	66	65																			
7	83	73	67	63	81	73	67	63	71	66	62	70	66	62	69	65	62	60																			
8	79	69	63	59	77	68	63	59	67	62	58	66	62	58	65	61	58	57																			
9	75	65	59	55	74	65	59	55	64	58	55	63	58	55	62	58	54	53																			
10	71	61	56	52	70	61	55	52	60	55	51	59	55	51	59	54	51	50																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	138805
5°	138918
10°	143809
15°	144052
20°	132621
25°	112997
30°	86510
35°	61116
40°	36071
45°	14648
50°	5303
55°	2953
60°	1683
65°	931
70°	990
75°	760
80°	818
85°	627

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 14648 cd/sqm



TEST NUMBER: P744707

CATALOG NUMBER: LD4D20D010-EU4DR6520359050-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	122.3	9.5
10°-20°	352.9	27.3
20°-30°	423.4	32.8
30°-40°	284.5	22.1
40°-50°	85.2	6.6
50°-60°	15.0	1.2
60°-70°	4.3	0.3
70°-80°	2.1	0.2
80°-90°	0.6	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	898.6	69.6
0°-40°	1183.1	91.7
0°-60°	1283.3	99.5
0°-90°	1290.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1290.3	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1270	
5°	1267	122
15°	1274	353
25°	937	423
35°	458	285
45°	95	85
55°	16	15
65°	4	4
75°	2	2
85°	0	1
90°	0	



TEST NUMBER: P744707

CATALOG NUMBER: LD4D20D010-EU4DR6520359050-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1270.4
2.5°	1275.8
5°	1266.6
7.5°	1285.8
10°	1296.2
12.5°	1293.7
15°	1273.5
17.5°	1224.0
20°	1140.6
22.5°	1042.4
25°	937.3
27.5°	818.7
30°	685.7
32.5°	565.0
35°	458.2
37.5°	352.6
40°	252.9
42.5°	165.2
45°	94.8
47.5°	50.2
50°	31.2
52.5°	21.7
55°	15.5
57.5°	11.2
60°	7.7
62.5°	5.0
65°	3.6
67.5°	3.3
70°	3.1
72.5°	2.3
75°	1.8
77.5°	1.6
80°	1.3
82.5°	0.9
85°	0.5
87.5°	0.3
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)