

Scaled data based on original data using

LM-41-14 Approved Method for Photometric Testing Of Indoor Fluorescent Luminaires

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: io LED

Report Number: P283527

Luminaire Tested: **LDA2B059727D010 EU2B05FL409727 2LBAPINSQ1MB**

Issue Date: 3/3/2020

Test Information

Test Method: LM-41-14
Report Number: P283527
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G2-1809-951-15)
Test Lab: INNOVATION CENTER(G2)
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: io LED
Catalog Number: LDA2B059727D010 EU2B05FL409727 2LBAPINSQ1MB
Description: PORTFOLIO 2IN ADJ 500 LUMEN LED LUMINAIRE WITH FLOOD OPTIC AND 2in Adj SQ PinHole, MB

Light Source: -
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 471.9 lumens
Efficiency: N/A
Efficacy: 67.4 lumens/watt
Spacing Criteria (0/90/45): 0.55 / 0.55 / 0.55
Luminous Opening: Circular (Dia: 0.17' x H: 0')
CIE Type: Direct


Input Watts (W): 7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P283527

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAPINSQ1MB

Luminous Intensity Polar Plot





TEST NUMBER: P283527

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAPINSQ1MB

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	114	112	110	108	112	110	108	106	106	104	103	102	101	100	99	98	97	95																			
2	110	106	102	99	108	104	101	98	101	98	96	98	96	94	95	93	92	90																			
3	105	100	96	92	104	99	95	92	96	93	90	94	91	89	92	89	88	86																			
4	101	95	90	87	100	94	90	86	92	88	85	90	87	84	88	86	83	82																			
5	98	91	86	82	96	90	85	82	88	84	81	86	83	80	85	82	80	79																			
6	94	87	82	78	93	86	81	78	84	80	77	83	80	77	82	79	76	75																			
7	91	83	78	75	89	82	78	74	81	77	74	80	76	74	79	76	73	72																			
8	87	80	75	71	86	79	74	71	78	74	71	77	73	71	76	73	70	69																			
9	84	77	72	69	83	76	72	68	75	71	68	74	71	68	74	70	68	67																			
10	82	74	69	66	81	73	69	66	73	69	66	72	68	65	71	68	65	64																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	621784	621784	621784
5°	595038	590581	595979
10°	506934	503778	507485
15°	373625	376077	374851
20°	233268	237574	228123
25°	120468	129287	114425
30°	57766	66197	55032
35°	29813	33005	27886
40°	16681	17582	15843
45°	10187	10187	9768
50°	5296	6524	5296
55°	2752	4301	2925
60°	3158	3158	3158
65°	3385	3385	3385
70°	4183	3750	4183
75°	4003	4003	4003
80°	3694	3694	3694
85°	2830	2830	2830



TEST NUMBER: P283527

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAPINSQ1MB

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	108.4	23.0
10°-20°	199.1	42.2
20°-30°	108.0	22.9
30°-40°	34.7	7.3
40°-50°	11.8	2.5
50°-60°	4.1	0.9
60°-70°	3.0	0.6
70°-80°	2.2	0.5
80°-90°	0.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	415.5	88.0
0°-40°	450.1	95.4
0°-60°	466.1	98.8
0°-90°	471.9	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	471.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1260	1260	1260	1260	1260	
5°	1202	1194	1192	1204	1203	109
15°	732	738	736	740	734	198
25°	221	231	238	221	210	106
35°	50	52	55	50	46	33
45°	15	15	15	15	14	12
55°	3	4	5	4	3	3
65°	3	3	3	3	3	3
75°	2	2	2	2	2	2
85°	0	0	0	0	0	1
90°	0	0	0	0	0	



TEST NUMBER: P283527

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAPINSQ1MB

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1260.3	1260.3	1260.3	1260.3	1260.3
1°	1258.2	1249.2	1247.8	1259.5	1256.8
2°	1248.1	1239.6	1238.3	1250.0	1247.6
3°	1237.0	1229.3	1226.7	1238.8	1237.3
4°	1222.2	1215.0	1212.6	1224.8	1223.5
5°	1201.5	1194.1	1192.5	1204.4	1203.4
6°	1176.1	1170.0	1167.1	1179.0	1176.9
7°	1144.3	1138.8	1135.6	1144.3	1145.4
8°	1103.0	1100.4	1096.7	1105.4	1105.4
9°	1059.1	1056.7	1052.7	1060.7	1060.7
10°	1011.9	1010.3	1005.6	1013.0	1013.0
11°	960.3	959.5	956.1	962.2	962.2
12°	906.0	907.9	904.7	910.0	908.1
13°	851.8	851.0	851.2	855.2	852.3
14°	790.3	795.1	795.9	798.3	793.8
15°	731.5	737.6	736.3	739.8	733.9
16°	671.4	678.3	678.1	678.9	673.3
17°	615.3	619.3	619.6	618.8	611.9
18°	555.5	561.0	561.0	559.7	551.5
19°	497.0	501.2	504.1	501.2	491.7
20°	444.3	447.2	452.5	445.1	434.5
21°	393.7	396.4	400.9	392.1	380.5
22°	345.3	348.7	352.9	342.9	330.7
23°	300.0	307.9	309.5	295.7	285.4
24°	258.4	267.4	270.1	256.0	245.2
25°	221.3	231.4	237.5	221.1	210.2
26°	189.3	199.1	206.5	190.1	179.8
27°	161.2	171.6	179.2	163.9	154.1
28°	137.1	147.2	155.2	140.9	131.6
29°	119.1	125.0	132.9	121.0	112.5
30°	101.4	107.8	116.2	104.1	96.6
32.5°	69.6	73.1	79.7	72.3	66.5
35°	49.5	51.6	54.8	49.8	46.3
37.5°	35.2	36.3	38.1	35.2	33.4
40°	25.9	26.5	27.3	25.7	24.6
42.5°	19.3	19.6	19.6	19.1	18.5
45°	14.6	14.8	14.6	14.6	14.0
47.5°	10.6	11.4	11.1	11.1	10.3
50°	6.9	8.5	8.5	8.2	6.9
52.5°	4.2	5.8	6.6	5.8	4.5
55°	3.2	4.0	5.0	4.0	3.4
57.5°	3.2	3.2	3.7	3.2	3.2
60°	3.2	3.2	3.2	3.2	3.2



TEST NUMBER: P283527

CATALOG NUMBER: LDA2B059727D010 EU2B05FL409727 2LBAPINSQ1MB

CANDELA DISTRIBUTION (continued):

	0°	22.5°	45°	67.5°	90°
67.5°	2.9	2.9	2.9	2.9	2.9
70°	2.9	2.9	2.6	2.9	2.9
72.5°	2.6	2.6	2.4	2.6	2.4
75°	2.1	2.1	2.1	2.1	2.1
77.5°	1.6	1.6	1.6	1.6	1.6
80°	1.3	1.3	1.3	1.3	1.3
82.5°	0.8	0.8	0.8	1.1	0.8
85°	0.5	0.5	0.5	0.5	0.5
87.5°	0.3	0.3	0.3	0.3	0.3
90°	0.0	0.0	0.0	0.0	0.0



Report Generated By E9808895 / USPTCWHP6082093





— 0°-180° - - 45°-225° - - - - 90°-270°







62.5°	3.2	3.2	3.2	3.2	3.2
65°	2.9	3.2	2.9	3.2	2.9



(END OF REPORT)