

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741961

Luminaire Tested: LD4D10D010-EU4DR200210IC9027-4LBS1B

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P741961  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D10D010-EU4DR200210IC9027-4LBS1B  
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1010.2 lumens  
Efficiency: N/A  
Efficacy: 86.3 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P741961  
CATALOG NUMBER: LD4D10D010-EU4DR200210IC9027-4LBS1B

### Luminous Intensity Polar Plot





TEST NUMBER: P741961

CATALOG NUMBER: LD4D10D010-EU4DR200210IC9027-4LBS1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20																	
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR																																													
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100									100																		
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	98	96	95	94	94	92	91	89	88	86	85	85	83														
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	92	91	89	88	86	85	85	83	81	80	79	77														
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	89	88	86	85	85	83	81	80	79	77	75	73	71														
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	86	85	85	83	81	80	79	77	75	73	71	69	67														
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	83	81	80	79	77	75	73	71	69	67	65	63														
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	81	80	79	77	75	73	71	69	67	65	63	61														
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	79	78	77	75	73	71	69	67	65	63	61	59														
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	77	76	75	73	71	69	67	65	63	61	59	57														
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	75	74	73	71	69	67	65	63	61	59	57	55														
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	73	72	71	69	67	65	63	61	59	57	55	53														

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	628260
5°	566806
10°	318127
15°	161709
20°	68461
25°	31610
30°	16729
35°	9017
40°	4821
45°	2843
50°	1649
55°	876
60°	568
65°	388
70°	160
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 2843 cd/sqm



TEST NUMBER: P741961

CATALOG NUMBER: LD4D10D010-EU4DR200210IC9027-4LBS1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	409.4	40.5
10°-20°	403.1	39.9
20°-30°	131.7	13.0
30°-40°	44.8	4.4
40°-50°	15.1	1.5
50°-60°	4.5	0.4
60°-70°	1.5	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	944.2	93.5
0°-40°	989.1	97.9
0°-60°	1008.6	99.8
0°-90°	1010.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1010.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	5750	
5°	5168	409
15°	1430	403
25°	262	132
35°	68	45
45°	18	15
55°	5	5
65°	2	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P741961  
CATALOG NUMBER: LD4D10D010-EU4DR200210IC9027-4LBS1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	5750.1
0.5°	5750.1
1°	5742.9
1.5°	5728.6
2°	5702.5
2.5°	5667.6
3°	5618.5
3.5°	5549.9
4°	5448.0
4.5°	5324.1
5°	5167.9
5.5°	4962.6
6°	4752.1
6.5°	4511.0
7°	4274.9
7.5°	3998.4
8°	3751.6
8.5°	3503.3
9°	3273.9
9.5°	3063.5
10°	2867.4
12.5°	2058.9
15°	1429.6
17.5°	933.9
20°	588.8
22.5°	381.5
25°	262.2
27.5°	184.3
30°	132.6
32.5°	95.2
35°	67.6
37.5°	47.1
40°	33.8
42.5°	24.6
45°	18.4
47.5°	14.3
50°	9.7
52.5°	6.1
55°	4.6
57.5°	3.6
60°	2.6
62.5°	2.0
65°	1.5



TEST NUMBER: P741961  
CATALOG NUMBER: LD4D10D010-EU4DR200210IC9027-4LBS1B

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		1.0
70°		0.5

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)