

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742584

Luminaire Tested: LD4D10D010-EU4DR600210IC9027-4LBDP1MW

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P742584  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D10D010-EU4DR600210IC9027-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 60° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 879.0 lumens  
Efficiency: N/A  
Efficacy: 75.1 lumens/watt  
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 11.7  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P742584  
CATALOG NUMBER: LD4D10D010-EU4DR600210IC9027-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P742584

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9027-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	114057
5°	116862
10°	118269
15°	112674
20°	99344
25°	80351
30°	54351
35°	27237
40°	4422
45°	4327
50°	4419
55°	4477
60°	4611
65°	4705
70°	4824
75°	4897
80°	4656
85°	4012

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 75°  
 Luminance: 4897 cd/sqm



TEST NUMBER: P742584

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9027-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	101.8	11.6
10°-20°	275.5	31.3
20°-30°	296.4	33.7
30°-40°	128.9	14.7
40°-50°	21.6	2.5
50°-60°	21.1	2.4
60°-70°	18.0	2.0
70°-80°	12.0	1.4
80°-90°	3.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	673.8	76.7
0°-40°	802.7	91.3
0°-60°	845.4	96.2
0°-90°	879.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	879.0	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	1044	
5°	1066	102
15°	996	276
25°	666	296
35°	204	129
45°	28	22
55°	24	21
65°	18	18
75°	12	12
85°	3	4
90°	0	



TEST NUMBER: P742584

CATALOG NUMBER: LD4D10D010-EU4DR600210IC9027-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	1043.9
2.5°	1073.3
5°	1065.5
7.5°	1067.9
10°	1066.0
12.5°	1044.0
15°	996.1
17.5°	931.7
20°	854.4
22.5°	771.7
25°	666.5
27.5°	533.1
30°	430.8
32.5°	332.0
35°	204.2
37.5°	87.4
40°	31.0
42.5°	28.5
45°	28.0
47.5°	27.0
50°	26.0
52.5°	24.8
55°	23.5
57.5°	22.3
60°	21.1
62.5°	19.7
65°	18.2
67.5°	16.7
70°	15.1
72.5°	13.3
75°	11.6
77.5°	9.5
80°	7.4
82.5°	5.3
85°	3.2
87.5°	1.1
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)