

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P741970

Luminaire Tested: LD4D10D010-EU4DR200210IC9030-4LBDP1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P741970
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D10D010-EU4DR200210IC9030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 907.8 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 11.7
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P741970

CATALOG NUMBER: LD4D10D010-EU4DR200210IC9030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P741970

CATALOG NUMBER: LD4D10D010-EU4DR200210IC9030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20				
RC	80				70				50				30				10			0	
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	97	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	94	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	91	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	88	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	85	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	83	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	81	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	79	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	77	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	564539
5°	509323
10°	285864
15°	145308
20°	61520
25°	28403
30°	15039
35°	8096
40°	4336
45°	2565
50°	1479
55°	781
60°	503
65°	362
70°	160
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 2565 cd/sqm



TEST NUMBER: P741970

CATALOG NUMBER: LD4D10D010-EU4DR200210IC9030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	367.9	40.5
10°-20°	362.2	39.9
20°-30°	118.3	13.0
30°-40°	40.3	4.4
40°-50°	13.6	1.5
50°-60°	4.1	0.4
60°-70°	1.4	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	848.5	93.5
0°-40°	888.7	97.9
0°-60°	906.4	99.8
0°-90°	907.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	907.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	5167	
5°	4644	368
15°	1285	362
25°	236	118
35°	61	40
45°	17	14
55°	4	4
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P741970

CATALOG NUMBER: LD4D10D010-EU4DR200210IC9030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	5166.9
0.5°	5166.9
1°	5160.5
1.5°	5147.6
2°	5124.1
2.5°	5092.8
3°	5048.7
3.5°	4987.0
4°	4895.5
4.5°	4784.1
5°	4643.8
5.5°	4459.3
6°	4270.2
6.5°	4053.5
7°	3841.4
7.5°	3592.9
8°	3371.1
8.5°	3148.0
9°	2941.9
9.5°	2752.8
10°	2576.6
12.5°	1850.1
15°	1284.6
17.5°	839.2
20°	529.1
22.5°	342.8
25°	235.6
27.5°	165.6
30°	119.2
32.5°	85.6
35°	60.7
37.5°	42.3
40°	30.4
42.5°	22.1
45°	16.6
47.5°	12.9
50°	8.7
52.5°	5.5
55°	4.1
57.5°	3.2
60°	2.3
62.5°	1.8
65°	1.4



TEST NUMBER: P741970

CATALOG NUMBER: LD4D10D010-EU4DR200210IC9030-4LBDP1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		0.9
70°		0.5

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)