

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739695

Luminaire Tested: LD4D02D010-EU4DR700210IC9027-4LBDP1B

Issue Date: 2/5/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P739695  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/5/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D02D010-EU4DR700210IC9027-4LBDP1B  
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 198.2 lumens  
Efficiency: N/A  
Efficacy: 38.9 lumens/watt  
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 5.1  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P739695  
CATALOG NUMBER: LD4D02D010-EU4DR700210IC9027-4LBDP1B

### Luminous Intensity Polar Plot





TEST NUMBER: P739695

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9027-4LBDP1B

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	24354
5°	23625
10°	22966
15°	22668
20°	21162
25°	15901
30°	11241
35°	3988
40°	2097
45°	2225
50°	2312
55°	2362
60°	2360
65°	2301
70°	2172
75°	2026
80°	1825
85°	1379

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 55°  
 Luminance: 2362 cd/sqm



TEST NUMBER: P739695

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9027-4LBDP1B

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	20.3	10.3
10°-20°	55.7	28.1
20°-30°	61.4	31.0
30°-40°	23.5	11.8
40°-50°	11.1	5.6
50°-60°	11.0	5.6
60°-70°	8.8	4.4
70°-80°	5.1	2.6
80°-90°	1.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	137.4	69.3
0°-40°	160.9	81.2
0°-60°	183.0	92.3
0°-90°	198.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	198.2	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	223	
5°	215	20
15°	200	56
25°	132	61
35°	30	23
45°	14	11
55°	12	11
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P739695

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9027-4LBDP1B

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	222.9
2.5°	220.5
5°	215.4
7.5°	211.1
10°	207.0
12.5°	203.5
15°	200.4
17.5°	192.8
20°	182.0
22.5°	158.8
25°	131.9
27.5°	114.8
30°	89.1
32.5°	57.5
35°	29.9
37.5°	16.1
40°	14.7
42.5°	14.6
45°	14.4
47.5°	14.1
50°	13.6
52.5°	13.0
55°	12.4
57.5°	11.6
60°	10.8
62.5°	9.9
65°	8.9
67.5°	7.9
70°	6.8
72.5°	5.8
75°	4.8
77.5°	3.8
80°	2.9
82.5°	2.0
85°	1.1
87.5°	0.5
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report





Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)