

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739164

Luminaire Tested: LD4D02D010-EU4DR350210IC9030-4LBDP1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P739164
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR350210IC9030-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 349.6 lumens
Efficiency: N/A
Efficacy: 68.5 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739164

CATALOG NUMBER: LD4D02D010-EU4DR350210IC9030-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P739164

CATALOG NUMBER: LD4D02D010-EU4DR350210IC9030-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									20								
RC	80									50									30									10									0								
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0															
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	99	98	98	96	96	96	92	92																
	1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96	96	96	96	95	93	93	92	92	92	88	88															
	2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92	92	92	96	95	93	93	91	89	89	88	88															
	3	106	101	97	94	105	100	96	93	97	94	92	95	93	91	93	91	89	88	88	88	87	85	83	87	84	82	81	81	81															
	4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84	84	84	89	85	83	87	84	82	81	81	81															
	5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81	81	81	89	85	83	87	84	82	81	81	81															
	6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78	78	78	84	81	79	84	81	79	78	78	78															
	7	93	85	81	77	91	85	80	77	84	80	77	83	79	77	82	79	76	75	75	75	82	79	77	82	79	76	75	75	75															
	8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72	72	72	79	76	74	79	76	73	72	72	72															
	9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70	70	70	77	73	71	77	73	71	70	70	70															
	10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68	68	68	74	71	69	74	71	69	68	68	68															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	105076
5°	102615
10°	92474
15°	71772
20°	40707
25°	15841
30°	5904
35°	3241
40°	2111
45°	1298
50°	816
55°	571
60°	415
65°	233
70°	32
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 1298 cd/sqm



TEST NUMBER: P739164

CATALOG NUMBER: LD4D02D010-EU4DR350210IC9030-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	24.6
10°-20°	168.0	48.1
20°-30°	68.5	19.6
30°-40°	16.4	4.7
40°-50°	6.8	2.0
50°-60°	2.8	0.8
60°-70°	0.9	0.3
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	322.5	92.3
0°-40°	338.9	97.0
0°-60°	348.6	99.7
0°-90°	349.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	349.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	962	
5°	936	86
15°	634	168
25°	131	69
35°	24	16
45°	8	7
55°	3	3
65°	1	1
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P739164

CATALOG NUMBER: LD4D02D010-EU4DR350210IC9030-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	961.7
2.5°	956.0
5°	935.6
7.5°	894.8
10°	833.5
12.5°	747.2
15°	634.5
17.5°	496.8
20°	350.1
22.5°	223.3
25°	131.4
27.5°	74.3
30°	46.8
32.5°	32.9
35°	24.3
37.5°	18.8
40°	14.8
42.5°	11.5
45°	8.4
47.5°	6.2
50°	4.8
52.5°	3.8
55°	3.0
57.5°	2.5
60°	1.9
62.5°	1.4
65°	0.9
67.5°	0.3
70°	0.1
72.5°	0.1
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.1
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)