

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739708

Luminaire Tested: LD4D02D010-EU4DR700210IC9030-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P739708
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR700210IC9030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 204.7 lumens
Efficiency: N/A
Efficacy: 40.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739708
CATALOG NUMBER: LD4D02D010-EU4DR700210IC9030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P739708
 CATALOG NUMBER: LD4D02D010-EU4DR700210IC9030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	25141
5°	24392
10°	23720
15°	23404
20°	21859
25°	16420
30°	11607
35°	4108
40°	2168
45°	2302
50°	2380
55°	2438
60°	2447
65°	2404
70°	2236
75°	2069
80°	1888
85°	1504

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 2447 cd/sqm



TEST NUMBER: P739708

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	21.0	10.2
10°-20°	57.6	28.1
20°-30°	63.4	31.0
30°-40°	24.2	11.8
40°-50°	11.5	5.6
50°-60°	11.4	5.6
60°-70°	9.1	4.4
70°-80°	5.2	2.6
80°-90°	1.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	141.9	69.3
0°-40°	166.1	81.2
0°-60°	189.0	92.3
0°-90°	204.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	204.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	230	
5°	222	21
15°	207	58
25°	136	63
35°	31	24
45°	15	11
55°	13	11
65°	9	9
75°	5	5
85°	1	1
90°	0	



TEST NUMBER: P739708

CATALOG NUMBER: LD4D02D010-EU4DR700210IC9030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

0°	
0°	230.1
2.5°	227.7
5°	222.4
7.5°	218.0
10°	213.8
12.5°	210.2
15°	206.9
17.5°	199.1
20°	188.0
22.5°	164.0
25°	136.2
27.5°	118.5
30°	92.0
32.5°	59.4
35°	30.8
37.5°	16.7
40°	15.2
42.5°	15.1
45°	14.9
47.5°	14.6
50°	14.0
52.5°	13.4
55°	12.8
57.5°	12.0
60°	11.2
62.5°	10.3
65°	9.3
67.5°	8.1
70°	7.0
72.5°	6.0
75°	4.9
77.5°	3.9
80°	3.0
82.5°	2.1
85°	1.2
87.5°	0.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)