

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739098

Luminaire Tested: LD4D02D010-EU4DR300210IC9035-4LBDP1H

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P739098
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR300210IC9035-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 359.3 lumens
Efficiency: N/A
Efficacy: 70.5 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739098

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9035-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P739098

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9035-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96						96													
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92						92													
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89						89													
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85						85													
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82						82													
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79						79													
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77						77													
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74						74													
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72						72													
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69						69													

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	88423	88423	88423
5°	85887	85787	85895
10°	74390	73869	74374
15°	48537	48275	48037
20°	24135	25040	24103
25°	12162	13707	11908
30°	4870	5303	4242
35°	2261	2159	1813
40°	969	1079	919
45°	693	855	693
50°	238	619	250
55°	133	254	147
60°	92	107	92
65°	54	54	54
70°	45	22	45
75°	0	30	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 855 cd/sqm



TEST NUMBER: P739098

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9035-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	101.6	28.3
10°-20°	163.6	45.5
20°-30°	70.7	19.7
30°-40°	16.1	4.5
40°-50°	5.5	1.5
50°-60°	1.4	0.4
60°-70°	0.3	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	335.9	93.5
0°-40°	352.0	98.0
0°-60°	358.9	99.9
0°-90°	359.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	359.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1155	1155	1155	1155	1155	
5°	1118	1117	1116	1119	1118	102
15°	612	605	609	607	606	164
25°	144	149	162	146	141	69
35°	24	25	23	23	19	16
45°	6	8	8	8	6	5
55°	1	1	2	1	1	1
65°	0	0	0	0	0	0
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P739098

CATALOG NUMBER: LD4D02D010-EU4DR300210IC9035-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	1155.2	1155.2	1155.2	1155.2	1155.2
2.5°	1147.6	1146.8	1147.3	1147.8	1148.1
5°	1117.8	1116.7	1116.5	1118.9	1117.9
7.5°	1057.8	1056.2	1053.9	1059.2	1064.1
10°	957.1	955.5	950.4	952.9	956.9
12.5°	808.6	803.1	803.0	810.9	809.9
15°	612.5	605.2	609.2	607.2	606.2
17.5°	411.9	409.1	414.5	412.9	405.8
20°	296.3	297.0	307.4	302.2	295.9
22.5°	216.2	218.9	231.2	217.7	212.8
25°	144.0	149.4	162.3	145.6	141.0
27.5°	88.5	91.0	104.2	87.4	84.9
30°	55.1	53.8	60.0	51.5	48.0
32.5°	36.2	34.5	36.6	32.8	30.0
35°	24.2	24.7	23.1	23.0	19.4
37.5°	15.1	17.4	15.3	16.3	12.5
40°	9.7	12.6	10.8	12.0	9.2
42.5°	8.0	9.7	8.9	9.5	8.2
45°	6.4	7.9	7.9	7.9	6.4
47.5°	3.5	5.3	6.8	5.4	3.7
50°	2.0	2.7	5.2	2.8	2.1
52.5°	1.4	1.5	3.6	1.6	1.4
55°	1.0	1.1	1.9	1.1	1.1
57.5°	0.8	0.9	1.0	0.9	0.8
60°	0.6	0.6	0.7	0.7	0.6
62.5°	0.5	0.5	0.5	0.5	0.5
65°	0.3	0.3	0.3	0.3	0.3
67.5°	0.2	0.2	0.2	0.2	0.2
70°	0.2	0.1	0.1	0.1	0.2
72.5°	0.1	0.1	0.1	0.1	0.1
75°	0.0	0.0	0.1	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)