

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739571

Luminaire Tested: LD4D02D010-EU4DR600210IC9035-4LBS1LI

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P739571
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-60)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR600210IC9035-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 407.8 lumens
Efficiency: N/A
Efficacy: 80.0 lumens/watt
Spacing Criteria (0/90/45): 0.98 / 0.98 / 0.92
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739571
CATALOG NUMBER: LD4D02D010-EU4DR600210IC9035-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P739571

CATALOG NUMBER: LD4D02D010-EU4DR600210IC9035-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR	0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100	100	100	100	100													
	1	114	111	108	106	111	109	106	104	105	103	101	101	99	98	97	96	95	94	94	94	94	94	94													
	2	108	103	99	96	106	101	98	95	98	95	92	95	93	90	92	90	89	87	87	87	87	87	87													
	3	102	96	91	87	100	95	90	86	92	88	85	90	86	84	87	85	82	81	81	81	81	81	81													
	4	97	90	84	80	95	88	83	79	86	82	78	84	81	78	82	79	77	75	75	75	75	75	75													
	5	92	84	78	74	91	83	77	73	81	76	73	79	75	72	78	74	71	70	70	70	70	70	70													
	6	87	79	73	68	86	78	72	68	76	71	68	75	70	67	74	70	67	65	65	65	65	65	65													
	7	83	74	68	63	82	73	67	63	72	67	63	71	66	63	69	65	62	61	61	61	61	61	61													
	8	79	69	63	59	78	69	63	59	68	63	59	67	62	59	66	61	58	57	57	57	57	57	57													
	9	75	65	59	55	74	65	59	55	64	59	55	63	58	55	62	58	55	53	53	53	53	53	53													
	10	72	62	56	52	71	61	56	52	61	55	52	60	55	52	59	55	52	50	50	50	50	50	50													

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	44589
5°	44474
10°	45954
15°	46004
20°	42335
25°	35998
30°	27428
35°	19407
40°	11396
45°	4589
50°	1547
55°	743
60°	306
65°	52
70°	0
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4589 cd/sqm



TEST NUMBER: P739571

CATALOG NUMBER: LD4D02D010-EU4DR600210IC9035-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	39.1	9.6
10°-20°	112.7	27.6
20°-30°	134.8	33.1
30°-40°	90.2	22.1
40°-50°	26.7	6.6
50°-60°	3.9	0.9
60°-70°	0.4	0.1
70°-80°	0.0	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	286.6	70.3
0°-40°	376.8	92.4
0°-60°	407.4	99.9
0°-90°	407.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	407.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	408	
5°	406	39
15°	407	113
25°	299	135
35°	146	90
45°	30	27
55°	4	4
65°	0	0
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P739571
CATALOG NUMBER: LD4D02D010-EU4DR600210IC9035-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	408.1
2.5°	407.6
5°	405.5
7.5°	411.0
10°	414.2
12.5°	413.7
15°	406.7
17.5°	390.4
20°	364.1
22.5°	332.5
25°	298.6
27.5°	260.5
30°	217.4
32.5°	179.0
35°	145.5
37.5°	111.8
40°	79.9
42.5°	52.7
45°	29.7
47.5°	15.2
50°	9.1
52.5°	5.8
55°	3.9
57.5°	2.5
60°	1.4
62.5°	0.6
65°	0.2
67.5°	0.1
70°	0.0
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)