

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P742897

Luminaire Tested: LD4D15D010-EU4DR1515309027-4LBS1LI

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P742897  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D15D010-EU4DR1515309027-4LBS1LI  
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 1451.7 lumens  
Efficiency: N/A  
Efficacy: 91.9 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 15.8  
Input Voltage (V): NR  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P742897  
CATALOG NUMBER: LD4D15D010-EU4DR1515309027-4LBS1LI

### Luminous Intensity Polar Plot





TEST NUMBER: P742897

CATALOG NUMBER: LD4D15D010-EU4DR1515309027-4LBS1LI

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100					100														
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98					98														
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96					96														
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94					94														
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93					93														
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92					92														
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90					90														
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89					89														
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88					88														
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87					87														
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86					86														

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	2225577	2225577	2225577
5°	1307852	1290921	1301135
10°	390334	393068	399086
15°	97089	98982	95925
20°	29047	33637	29669
25°	10244	13048	10369
30°	3759	4950	3826
35°	1888	2128	1823
40°	1186	1307	1186
45°	882	938	882
50°	695	695	695
55°	585	585	585
60°	470	470	470
65°	357	357	357
70°	307	307	307
75°	189	189	249
80°	134	134	134
85°	66	66	66

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°

Vertical Angle: 45°

Luminance: 938 cd/sqm



TEST NUMBER: P742897

CATALOG NUMBER: LD4D15D010-EU4DR1515309027-4LBS1LI

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	941.5	64.9
10°-20°	387.3	26.7
20°-30°	76.9	5.3
30°-40°	19.2	1.3
40°-50°	10.1	0.7
50°-60°	7.5	0.5
60°-70°	5.3	0.4
70°-80°	3.0	0.2
80°-90°	0.9	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1405.7	96.8
0°-40°	1424.9	98.2
0°-60°	1442.5	99.4
0°-90°	1451.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1451.7	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	19779	19779	19779	19779	19779	
5°	12869	12737	12702	12790	12803	940
15°	1118	1139	1140	1120	1104	383
25°	132	149	168	148	133	69
35°	26	28	29	28	25	18
45°	13	13	13	13	13	10
55°	8	8	8	8	8	7
65°	5	5	5	5	5	5
75°	2	2	2	2	3	3
85°	1	1	1	1	1	1
90°	0	0	0	0	0	



TEST NUMBER: P742897

CATALOG NUMBER: LD4D15D010-EU4DR1515309027-4LBS1LI

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	19779.4	19779.4	19779.4	19779.4	19779.4
2.5°	17841.8	17856.9	17862.7	17880.3	17945.6
5°	12868.9	12736.6	12702.3	12790.2	12802.8
7.5°	7623.0	7649.8	7747.8	7769.6	7690.9
10°	4183.3	4217.6	4212.6	4242.7	4277.1
12.5°	2139.4	2112.6	2104.2	2138.5	2090.8
15°	1117.8	1138.8	1139.6	1119.5	1104.4
17.5°	601.2	625.5	665.7	633.0	582.8
20°	355.0	376.8	411.1	384.3	362.6
22.5°	219.4	237.0	261.2	240.3	222.7
25°	131.5	149.0	167.5	148.2	133.1
27.5°	77.9	92.9	104.7	92.1	77.0
30°	50.2	58.6	66.1	57.8	51.1
32.5°	35.2	38.5	41.9	38.5	35.2
35°	26.0	27.6	29.3	27.6	25.1
37.5°	20.1	21.8	22.6	20.9	19.3
40°	16.7	17.6	18.4	17.6	16.7
42.5°	14.2	15.1	15.1	15.1	14.2
45°	12.6	12.6	13.4	12.6	12.6
47.5°	10.9	10.9	11.7	10.9	10.9
50°	10.0	10.0	10.0	10.0	10.0
52.5°	9.2	9.2	9.2	9.2	9.2
55°	8.4	8.4	8.4	8.4	8.4
57.5°	7.5	7.5	7.5	7.5	7.5
60°	6.7	6.7	6.7	6.7	6.7
62.5°	5.9	5.9	5.9	5.9	5.9
65°	5.0	5.0	5.0	5.0	5.0
67.5°	5.0	5.0	5.0	5.0	5.0
70°	4.2	4.2	4.2	4.2	4.2
72.5°	3.3	3.3	3.3	3.3	3.3
75°	2.5	2.5	2.5	2.5	3.3
77.5°	2.5	2.5	2.5	2.5	2.5
80°	1.7	1.7	1.7	1.7	1.7
82.5°	1.7	1.7	1.7	1.7	1.7
85°	0.8	0.8	0.8	0.8	0.8
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)