

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P739674

Luminaire Tested: LD4D02D010-EU4DR650210IC9050-4LBS1H

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P739674
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-147)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D02D010-EU4DR650210IC9050-4LBS1H
Description: 4 INCH ROUND SHALLOW SEMI-SPECULAR CLEAR TRIM, WITH 65° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 344.6 lumens
Efficiency: N/A
Efficacy: 67.6 lumens/watt
Spacing Criteria (0/90/45): 0.95 / 0.95 / 0.96
Luminous Opening: Circular (Dia: 0.48' x H: 0')
CIE Type: Direct

Input Watts (W): 5.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P739674
CATALOG NUMBER: LD4D02D010-EU4DR650210IC9050-4LBS1H

Luminous Intensity Polar Plot





TEST NUMBER: P739674

CATALOG NUMBER: LD4D02D010-EU4DR650210IC9050-4LBS1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100				100															
1	113	110	107	105	111	108	105	103	104	102	100	100	99	97	97	95	94	93				93															
2	107	102	97	94	105	100	96	92	97	93	90	94	91	88	91	89	87	85				85															
3	101	94	88	84	99	92	87	83	90	86	82	87	84	81	85	82	80	78				78															
4	95	87	81	76	93	86	80	76	84	79	75	82	77	74	80	76	73	72				72															
5	90	81	74	70	88	80	74	69	78	73	69	76	72	68	75	71	68	66				66															
6	85	75	69	64	83	74	68	64	73	67	63	71	67	63	70	66	62	61				61															
7	80	70	64	59	79	69	63	59	68	63	59	67	62	58	66	61	58	56				56															
8	76	66	59	55	75	65	59	55	64	58	54	63	58	54	62	57	54	52				52															
9	72	61	55	51	71	61	55	51	60	54	51	59	54	50	58	54	50	49				49															
10	68	58	52	47	67	57	51	47	57	51	47	56	51	47	55	50	47	46				46															

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	18275
5°	18227
10°	18213
15°	17649
20°	16073
25°	14003
30°	11647
35°	9226
40°	6663
45°	4204
50°	2190
55°	1171
60°	607
65°	345
70°	137
75°	158
80°	101
85°	67

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4204 cd/sqm



TEST NUMBER: P739674

CATALOG NUMBER: LD4D02D010-EU4DR650210IC9050-4LBS1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	29.6	8.6
10°-20°	81.0	23.5
20°-30°	99.0	28.7
30°-40°	80.4	23.3
40°-50°	40.0	11.6
50°-60°	11.2	3.2
60°-70°	2.6	0.7
70°-80°	0.7	0.2
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	209.7	60.8
0°-40°	290.0	84.2
0°-60°	341.2	99.0
0°-90°	344.6	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	344.6	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	313	
5°	311	30
15°	292	81
25°	217	99
35°	129	80
45°	51	40
55°	12	11
65°	2	3
75°	1	1
85°	0	0
90°	0	



TEST NUMBER: P739674

CATALOG NUMBER: LD4D02D010-EU4DR650210IC9050-4LBS1H

CANDELA DISTRIBUTION (FULL):

0°	
0°	312.9
2.5°	312.7
5°	310.9
7.5°	309.9
10°	307.1
12.5°	301.4
15°	291.9
17.5°	277.1
20°	258.6
22.5°	238.5
25°	217.3
27.5°	194.6
30°	172.7
32.5°	151.0
35°	129.4
37.5°	107.9
40°	87.4
42.5°	68.1
45°	50.9
47.5°	35.5
50°	24.1
52.5°	16.7
55°	11.5
57.5°	7.7
60°	5.2
62.5°	3.6
65°	2.5
67.5°	1.3
70°	0.8
72.5°	0.8
75°	0.7
77.5°	0.5
80°	0.3
82.5°	0.2
85°	0.1
87.5°	0.1
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)