

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743577

Luminaire Tested: LD4D15D010-EU4DR600215IC9027-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743577
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-57)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR600215IC9027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 60° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1369.4 lumens
Efficiency: N/A
Efficacy: 86.7 lumens/watt
Spacing Criteria (0/90/45): 0.91 / 0.91 / 0.83
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743577

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P743577

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	113	110	108	105	111	108	106	104	104	102	100	100	99	97	97	96	95	93																			
2	107	102	98	95	105	101	97	94	97	94	92	94	92	90	92	90	88	86																			
3	102	96	90	86	100	94	89	86	91	88	84	89	86	83	87	84	82	80																			
4	97	89	84	80	95	88	83	79	86	82	78	84	80	77	82	79	76	75																			
5	92	84	78	74	91	83	78	74	81	77	73	80	76	72	78	75	72	70																			
6	88	79	73	69	87	78	73	69	77	72	68	75	71	68	74	70	67	66																			
7	84	75	69	65	83	74	68	64	73	68	64	72	67	64	71	67	63	62																			
8	80	71	65	61	79	70	65	61	69	64	60	68	64	60	67	63	60	59																			
9	77	67	61	57	75	67	61	57	66	61	57	65	60	57	64	60	57	55																			
10	73	64	58	54	72	63	58	54	62	58	54	62	57	54	61	57	54	53																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	177702
5°	182066
10°	184271
15°	175532
20°	154771
25°	125185
30°	84681
35°	42429
40°	6875
45°	6737
50°	6884
55°	6972
60°	7168
65°	7342
70°	7507
75°	7599
80°	7299
85°	6143

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 75°
 Luminance: 7599 cd/sqm



TEST NUMBER: P743577

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	158.7	11.6
10°-20°	429.2	31.3
20°-30°	461.8	33.7
30°-40°	200.8	14.7
40°-50°	33.7	2.5
50°-60°	32.8	2.4
60°-70°	28.0	2.0
70°-80°	18.7	1.4
80°-90°	5.6	0.4
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1049.7	76.7
0°-40°	1250.5	91.3
0°-60°	1317.0	96.2
0°-90°	1369.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1369.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1626	
5°	1660	159
15°	1552	429
25°	1038	462
35°	318	201
45°	44	34
55°	37	33
65°	28	28
75°	18	19
85°	5	6
90°	0	



TEST NUMBER: P743577

CATALOG NUMBER: LD4D15D010-EU4DR600215IC9027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1626.4
2.5°	1672.1
5°	1660.0
7.5°	1663.8
10°	1660.9
12.5°	1626.6
15°	1551.8
17.5°	1451.5
20°	1331.1
22.5°	1202.2
25°	1038.4
27.5°	830.5
30°	671.2
32.5°	517.3
35°	318.1
37.5°	136.1
40°	48.2
42.5°	44.5
45°	43.6
47.5°	42.1
50°	40.5
52.5°	38.5
55°	36.6
57.5°	34.7
60°	32.8
62.5°	30.7
65°	28.4
67.5°	26.0
70°	23.5
72.5°	20.7
75°	18.0
77.5°	14.8
80°	11.6
82.5°	8.3
85°	4.9
87.5°	1.7
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)