

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743726

Luminaire Tested: LD4D15D010-EU4DR700215IC9027-4LBDP1MW

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743726
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9027-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1025.3 lumens
Efficiency: N/A
Efficacy: 64.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743726

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9027-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P743726

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9027-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																												
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																												
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																												
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																												
5	89	80	74	69	88	79	73	69	77	72	68	75	71	67	74	70	67	65																												
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																												
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																												
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																												
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																												
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	125956
5°	122214
10°	118812
15°	117255
20°	109483
25°	82255
30°	58149
35°	20594
40°	10826
45°	11542
50°	11933
55°	12172
60°	12237
65°	11996
70°	11309
75°	10469
80°	9312
85°	7522

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 12242 cd/sqm



TEST NUMBER: P743726

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9027-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.1	10.3
10°-20°	288.3	28.1
20°-30°	317.5	31.0
30°-40°	121.3	11.8
40°-50°	57.3	5.6
50°-60°	56.9	5.6
60°-70°	45.6	4.4
70°-80°	26.2	2.6
80°-90°	7.1	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	710.9	69.3
0°-40°	832.2	81.2
0°-60°	946.4	92.3
0°-90°	1025.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1025.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1153	
5°	1114	105
15°	1037	288
25°	682	318
35°	154	121
45°	75	57
55°	64	57
65°	46	46
75°	25	26
85°	6	7
90°	0	



TEST NUMBER: P743726

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9027-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

	0°
0°	1152.8
2.5°	1140.8
5°	1114.3
7.5°	1092.2
10°	1070.9
12.5°	1052.8
15°	1036.6
17.5°	997.3
20°	941.6
22.5°	821.6
25°	682.3
27.5°	593.9
30°	460.9
32.5°	297.7
35°	154.4
37.5°	83.4
40°	75.9
42.5°	75.4
45°	74.7
47.5°	73.0
50°	70.2
52.5°	67.1
55°	63.9
57.5°	60.2
60°	56.0
62.5°	51.3
65°	46.4
67.5°	40.9
70°	35.4
72.5°	29.9
75°	24.8
77.5°	19.5
80°	14.8
82.5°	10.4
85°	6.0
87.5°	2.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)