

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743139

Luminaire Tested: LD4D15D010-EU4DR300215IC9030-4LBS1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P743139
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-16)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR300215IC9030-4LBS1MW
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 30° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1312.1 lumens
Efficiency: N/A
Efficacy: 83.0 lumens/watt
Spacing Criteria (0/90/45): 0.52 / 0.52 / 0.49
Luminous Opening: Rectangular (W 0.38' x L: 0.38' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743139
CATALOG NUMBER: LD4D15D010-EU4DR300215IC9030-4LBS1MW

Luminous Intensity Polar Plot





TEST NUMBER: P743139

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9030-4LBS1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20										
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100								
1	115	113	111	109	112	110	109	107	106	105	104	103	102	101	99	99	98	96								
2	111	107	104	101	109	105	102	100	102	100	98	99	97	96	97	95	94	92								
3	107	102	98	95	105	101	97	94	98	95	93	96	93	91	94	92	90	89								
4	103	98	93	90	102	96	93	90	94	91	89	93	90	88	91	89	87	85								
5	100	94	89	86	98	93	89	86	91	88	85	90	86	84	88	86	83	82								
6	97	90	85	82	95	89	85	82	88	84	81	87	83	81	85	83	80	79								
7	94	87	82	79	92	86	82	79	85	81	78	84	81	78	83	80	78	77								
8	91	84	79	76	90	83	79	76	82	78	76	81	78	75	80	77	75	74								
9	88	81	76	73	87	80	76	73	80	76	73	79	75	73	78	75	73	72								
10	85	78	74	71	85	78	74	71	77	73	71	76	73	71	76	73	70	69								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	322937	322937	322937
5°	313667	313306	313690
10°	271685	269773	271623
15°	177260	176309	175421
20°	88143	91450	88021
25°	44399	50066	43495
30°	17783	19374	15494
35°	8242	7896	6616
40°	3557	3957	3357
45°	2511	3118	2533
50°	869	2274	917
55°	494	934	534
60°	352	413	352
65°	235	235	235
70°	134	90	134
75°	0	59	0
80°	0	0	0
85°	0	0	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 22.5°

Vertical Angle: 45°

Luminance: 3118 cd/sqm



TEST NUMBER: P743139

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9030-4LBS1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	371.0	28.3
10°-20°	597.5	45.5
20°-30°	258.2	19.7
30°-40°	58.8	4.5
40°-50°	20.2	1.5
50°-60°	4.9	0.4
60°-70°	1.3	0.1
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1226.7	93.5
0°-40°	1285.6	98.0
0°-60°	1310.7	99.9
0°-90°	1312.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1312.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	4219	4219	4219	4219	4219	
5°	4082	4078	4078	4086	4083	371
15°	2237	2210	2225	2218	2214	599
25°	526	546	593	532	515	252
35°	88	90	84	84	71	60
45°	23	29	29	29	23	16
55°	4	4	7	4	4	4
65°	1	1	1	1	1	1
75°	0	0	0	0	0	0
85°	0	0	0	0	0	0
90°	0	0	0	0	0	



TEST NUMBER: P743139

CATALOG NUMBER: LD4D15D010-EU4DR300215IC9030-4LBS1MW

CANDELA DISTRIBUTION (FULL):

	0°	22.5°	45°	67.5°	90°
0°	4219.0	4219.0	4219.0	4219.0	4219.0
2.5°	4191.1	4188.2	4189.9	4191.9	4192.7
5°	4082.3	4078.4	4077.6	4086.1	4082.6
7.5°	3863.0	3857.4	3848.9	3868.2	3886.2
10°	3495.5	3489.3	3470.9	3480.0	3494.7
12.5°	2953.0	2932.9	2932.5	2961.5	2957.6
15°	2236.9	2210.0	2224.9	2217.7	2213.7
17.5°	1504.3	1493.9	1513.8	1507.8	1481.9
20°	1082.1	1084.8	1122.7	1103.7	1080.6
22.5°	789.6	799.4	844.3	795.2	777.2
25°	525.7	545.6	592.8	531.8	515.0
27.5°	323.4	332.5	380.3	319.2	310.1
30°	201.2	196.6	219.2	188.1	175.3
32.5°	132.0	126.2	133.4	119.7	109.4
35°	88.2	90.1	84.5	83.9	70.8
37.5°	55.1	63.4	55.9	59.6	45.5
40°	35.6	46.0	39.6	43.7	33.6
42.5°	29.2	35.4	32.5	34.6	29.9
45°	23.2	28.8	28.8	28.8	23.4
47.5°	12.8	19.3	24.6	19.7	13.7
50°	7.3	9.7	19.1	10.1	7.7
52.5°	5.0	5.6	13.1	5.8	5.2
55°	3.7	4.0	7.0	4.1	4.0
57.5°	2.9	3.1	3.7	3.1	2.9
60°	2.3	2.3	2.7	2.5	2.3
62.5°	1.7	1.7	1.9	1.7	1.7
65°	1.3	1.3	1.3	1.3	1.3
67.5°	0.6	0.8	0.8	0.8	0.8
70°	0.6	0.4	0.4	0.4	0.6
72.5°	0.4	0.2	0.2	0.2	0.2
75°	0.0	0.0	0.2	0.0	0.0
77.5°	0.0	0.0	0.0	0.0	0.0
80°	0.0	0.0	0.0	0.0	0.0
82.5°	0.0	0.0	0.0	0.0	0.0
85°	0.0	0.0	0.0	0.0	0.0
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180° - - 45°-225° - - - 90°-270°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)