

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745657

Luminaire Tested: LD4D25D010-EU4DR7020359024-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745657
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR7020359024-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2098.4 lumens
Efficiency: N/A
Efficacy: 83.6 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745657
CATALOG NUMBER: LD4D25D010-EU4DR7020359024-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P745657

CATALOG NUMBER: LD4D25D010-EU4DR7020359024-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	257768
5°	250110
10°	243139
15°	239951
20°	224058
25°	168320
30°	118985
35°	42149
40°	22165
45°	23595
50°	24443
55°	24897
60°	25043
65°	24535
70°	23161
75°	21445
80°	19065
85°	15420

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 25053 cd/sqm



TEST NUMBER: P745657

CATALOG NUMBER: LD4D25D010-EU4DR7020359024-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	215.1	10.3
10°-20°	590.0	28.1
20°-30°	649.8	31.0
30°-40°	248.3	11.8
40°-50°	117.2	5.6
50°-60°	116.5	5.6
60°-70°	93.3	4.4
70°-80°	53.6	2.6
80°-90°	14.6	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1454.9	69.3
0°-40°	1703.1	81.2
0°-60°	1936.8	92.3
0°-90°	2098.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2098.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2359	
5°	2280	215
15°	2121	590
25°	1396	650
35°	316	248
45°	153	117
55°	131	117
65°	95	93
75°	51	54
85°	12	15
90°	0	



TEST NUMBER: P745657

CATALOG NUMBER: LD4D25D010-EU4DR7020359024-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2359.2
2.5°	2334.5
5°	2280.4
7.5°	2235.2
10°	2191.5
12.5°	2154.5
15°	2121.3
17.5°	2041.0
20°	1927.0
22.5°	1681.3
25°	1396.2
27.5°	1215.5
30°	943.1
32.5°	609.2
35°	316.0
37.5°	170.7
40°	155.4
42.5°	154.3
45°	152.7
47.5°	149.4
50°	143.8
52.5°	137.5
55°	130.7
57.5°	123.2
60°	114.6
62.5°	105.0
65°	94.9
67.5°	83.7
70°	72.5
72.5°	61.2
75°	50.8
77.5°	40.0
80°	30.3
82.5°	21.3
85°	12.3
87.5°	4.9
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)