

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744895

Luminaire Tested: LD4D25D010-EU4DR2015309027-4LBS1LI

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P744895
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR2015309027-4LBS1LI
Description: 4 INCH ROUND SHALLOW SPECULAR CLEAR TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2702.8 lumens
Efficiency: N/A
Efficacy: 107.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744895
CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBS1LI

Luminous Intensity Polar Plot





TEST NUMBER: P744895

CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBS1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20		
RC	80				70				50				30				10		0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	0
RCR																			
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1680824
5°	1516421
10°	851102
15°	432631
20°	183165
25°	84558
30°	44763
35°	24116
40°	12894
45°	7618
50°	4419
55°	2343
60°	1486
65°	1060
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7618 cd/sqm



TEST NUMBER: P744895

CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBS1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1095.3	40.5
10°-20°	1078.5	39.9
20°-30°	352.3	13.0
30°-40°	119.9	4.4
40°-50°	40.3	1.5
50°-60°	12.1	0.4
60°-70°	4.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2526.1	93.5
0°-40°	2646.1	97.9
0°-60°	2698.6	99.8
0°-90°	2702.8	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2702.8	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15384	
5°	13826	###
15°	3825	1079
25°	701	352
35°	181	120
45°	49	40
55°	12	12
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P744895

CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBS1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	15383.6
0.5°	15383.6
1°	15364.4
1.5°	15326.1
2°	15256.2
2.5°	15163.1
3°	15031.6
3.5°	14848.0
4°	14575.4
4.5°	14243.9
5°	13826.1
5.5°	13276.8
6°	12713.7
6.5°	12068.5
7°	11437.0
7.5°	10697.3
8°	10037.0
8.5°	9372.6
9°	8758.9
9.5°	8195.9
10°	7671.3
12.5°	5508.2
15°	3824.7
17.5°	2498.6
20°	1575.3
22.5°	1020.6
25°	701.4
27.5°	493.2
30°	354.8
32.5°	254.8
35°	180.8
37.5°	126.0
40°	90.4
42.5°	65.8
45°	49.3
47.5°	38.4
50°	26.0
52.5°	16.4
55°	12.3
57.5°	9.6
60°	6.8
62.5°	5.5
65°	4.1



TEST NUMBER: P744895
CATALOG NUMBER: LD4D25D010-EU4DR2015309027-4LBS1LI

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		2.7
70°		1.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)