

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743737

Luminaire Tested: LD4D15D010-EU4DR700215IC9030-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743737
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1355.5 lumens
Efficiency: N/A
Efficacy: 85.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743737

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P743737

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	166513
5°	161567
10°	157056
15°	155002
20°	144736
25°	108729
30°	76871
35°	27223
40°	14320
45°	15251
50°	15791
55°	16096
60°	16192
65°	15848
70°	14951
75°	13847
80°	12270
85°	10029

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 16192 cd/sqm



TEST NUMBER: P743737

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	138.9	10.2
10°-20°	381.1	28.1
20°-30°	419.7	31.0
30°-40°	160.4	11.8
40°-50°	75.7	5.6
50°-60°	75.3	5.6
60°-70°	60.3	4.4
70°-80°	34.6	2.6
80°-90°	9.5	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	939.8	69.3
0°-40°	1100.2	81.2
0°-60°	1251.2	92.3
0°-90°	1355.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1355.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1524	
5°	1473	139
15°	1370	381
25°	902	420
35°	204	160
45°	99	76
55°	84	75
65°	61	60
75°	33	35
85°	8	9
90°	0	



TEST NUMBER: P743737

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	1524.0
2.5°	1508.1
5°	1473.1
7.5°	1443.9
10°	1415.6
12.5°	1391.8
15°	1370.3
17.5°	1318.4
20°	1244.8
22.5°	1086.0
25°	901.9
27.5°	785.2
30°	609.3
32.5°	393.6
35°	204.1
37.5°	110.3
40°	100.4
42.5°	99.6
45°	98.7
47.5°	96.5
50°	92.9
52.5°	88.8
55°	84.5
57.5°	79.6
60°	74.1
62.5°	67.8
65°	61.3
67.5°	54.0
70°	46.8
72.5°	39.6
75°	32.8
77.5°	25.8
80°	19.5
82.5°	13.8
85°	8.0
87.5°	3.2
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)