

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743750

Luminaire Tested: LD4D15D010-EU4DR700215IC9035-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P743750
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D15D010-EU4DR700215IC9035-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1502.5 lumens
Efficiency: N/A
Efficacy: 95.1 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 15.8
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743750

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9035-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P743750

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9035-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	184574
5°	179093
10°	174097
15°	171810
20°	160433
25°	120520
30°	85198
35°	30185
40°	15875
45°	16904
50°	17508
55°	17830
60°	17941
65°	17580
70°	16580
75°	15366
80°	13654
85°	11032

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 17941 cd/sqm



TEST NUMBER: P743750

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9035-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.0	10.3
10°-20°	422.4	28.1
20°-30°	465.3	31.0
30°-40°	177.8	11.8
40°-50°	84.0	5.6
50°-60°	83.4	5.6
60°-70°	66.8	4.4
70°-80°	38.4	2.6
80°-90°	10.4	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1041.7	69.3
0°-40°	1219.5	81.2
0°-60°	1386.9	92.3
0°-90°	1502.5	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1502.5	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1689	
5°	1633	154
15°	1519	422
25°	1000	465
35°	226	178
45°	109	84
55°	94	83
65°	68	67
75°	36	38
85°	9	10
90°	0	



TEST NUMBER: P743750

CATALOG NUMBER: LD4D15D010-EU4DR700215IC9035-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

0°	
0°	1689.3
2.5°	1671.6
5°	1632.9
7.5°	1600.5
10°	1569.2
12.5°	1542.7
15°	1518.9
17.5°	1461.4
20°	1379.8
22.5°	1203.8
25°	999.7
27.5°	870.3
30°	675.3
32.5°	436.2
35°	226.3
37.5°	122.2
40°	111.3
42.5°	110.5
45°	109.4
47.5°	107.0
50°	103.0
52.5°	98.4
55°	93.6
57.5°	88.2
60°	82.1
62.5°	75.2
65°	68.0
67.5°	59.9
70°	51.9
72.5°	43.9
75°	36.4
77.5°	28.6
80°	21.7
82.5°	15.2
85°	8.8
87.5°	3.5
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)