

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745682

Luminaire Tested: LD4D25D010-EU4DR7020359030-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745682
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR7020359030-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1399.4 lumens
Efficiency: N/A
Efficacy: 55.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745682
CATALOG NUMBER: LD4D25D010-EU4DR7020359030-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P745682

CATALOG NUMBER: LD4D25D010-EU4DR7020359030-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	171900
5°	166798
10°	162148
15°	160024
20°	149422
25°	112262
30°	79357
35°	28104
40°	14776
45°	15745
50°	16301
55°	16611
60°	16717
65°	16365
70°	15430
75°	14311
80°	12710
85°	10280

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 16717 cd/sqm



TEST NUMBER: P745682

CATALOG NUMBER: LD4D25D010-EU4DR7020359030-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	143.4	10.2
10°-20°	393.5	28.1
20°-30°	433.3	31.0
30°-40°	165.6	11.8
40°-50°	78.2	5.6
50°-60°	77.7	5.6
60°-70°	62.2	4.4
70°-80°	35.8	2.6
80°-90°	9.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	970.2	69.3
0°-40°	1135.8	81.2
0°-60°	1291.7	92.3
0°-90°	1399.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1399.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1573	
5°	1521	143
15°	1415	393
25°	931	433
35°	211	166
45°	102	78
55°	87	78
65°	63	62
75°	34	36
85°	8	10
90°	0	



TEST NUMBER: P745682

CATALOG NUMBER: LD4D25D010-EU4DR7020359030-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1573.3
2.5°	1556.9
5°	1520.8
7.5°	1490.6
10°	1461.5
12.5°	1436.8
15°	1414.7
17.5°	1361.1
20°	1285.1
22.5°	1121.2
25°	931.2
27.5°	810.6
30°	629.0
32.5°	406.3
35°	210.7
37.5°	113.8
40°	103.6
42.5°	102.9
45°	101.9
47.5°	99.6
50°	95.9
52.5°	91.7
55°	87.2
57.5°	82.2
60°	76.5
62.5°	70.0
65°	63.3
67.5°	55.8
70°	48.3
72.5°	40.9
75°	33.9
77.5°	26.6
80°	20.2
82.5°	14.2
85°	8.2
87.5°	3.3
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)