

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745683

Luminaire Tested: LD4D25D010-EU4DR7020359030-4LBDP1H

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P745683
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR7020359030-4LBDP1H
Description: 4 INCH ROUND DEEP 45° CUTOFF SEMI-SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2405.2 lumens
Efficiency: N/A
Efficacy: 95.8 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745683
CATALOG NUMBER: LD4D25D010-EU4DR7020359030-4LBDP1H

Luminous Intensity Polar Plot





TEST NUMBER: P745683

CATALOG NUMBER: LD4D25D010-EU4DR7020359030-4LBDP1H

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	295463
5°	286688
10°	278686
15°	275028
20°	256824
25°	192938
30°	136383
35°	48311
40°	25402
45°	27056
50°	28013
55°	28535
60°	28714
65°	28103
70°	26547
75°	24569
80°	21834
85°	17801

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 28734 cd/sqm



TEST NUMBER: P745683

CATALOG NUMBER: LD4D25D010-EU4DR7020359030-4LBDP1H

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	246.5	10.3
10°-20°	676.2	28.1
20°-30°	744.8	31.0
30°-40°	284.6	11.8
40°-50°	134.4	5.6
50°-60°	133.6	5.6
60°-70°	106.9	4.4
70°-80°	61.5	2.6
80°-90°	16.7	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1667.6	69.3
0°-40°	1952.1	81.2
0°-60°	2220.1	92.3
0°-90°	2405.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2405.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2704	
5°	2614	247
15°	2431	676
25°	1600	745
35°	362	285
45°	175	134
55°	150	134
65°	109	107
75°	58	61
85°	14	17
90°	0	



TEST NUMBER: P745683

CATALOG NUMBER: LD4D25D010-EU4DR7020359030-4LBDP1H

CANDELA DISTRIBUTION (FULL):

	0°
0°	2704.2
2.5°	2675.9
5°	2613.9
7.5°	2562.0
10°	2511.9
12.5°	2469.5
15°	2431.4
17.5°	2339.4
20°	2208.8
22.5°	1927.1
25°	1600.4
27.5°	1393.2
30°	1081.0
32.5°	698.3
35°	362.2
37.5°	195.7
40°	178.1
42.5°	176.8
45°	175.1
47.5°	171.3
50°	164.8
52.5°	157.6
55°	149.8
57.5°	141.3
60°	131.4
62.5°	120.3
65°	108.7
67.5°	95.9
70°	83.1
72.5°	70.2
75°	58.2
77.5°	45.8
80°	34.7
82.5°	24.4
85°	14.2
87.5°	5.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)