

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P743944

Luminaire Tested: LD4D20D010-EU4DR2015309024-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P743944
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR2015309024-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2400K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1679.3 lumens
Efficiency: N/A
Efficacy: 72.7 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P743944
CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P743944

CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1044271
5°	942124
10°	528770
15°	268784
20°	113796
25°	52538
30°	27806
35°	14979
40°	8016
45°	4728
50°	2754
55°	1467
60°	940
65°	672
70°	288
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 4728 cd/sqm



TEST NUMBER: P743944

CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	680.5	40.5
10°-20°	670.1	39.9
20°-30°	218.9	13.0
30°-40°	74.5	4.4
40°-50°	25.1	1.5
50°-60°	7.6	0.5
60°-70°	2.5	0.2
70°-80°	0.1	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1569.5	93.5
0°-40°	1644.0	97.9
0°-60°	1676.6	99.8
0°-90°	1679.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1679.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	9558	
5°	8590	680
15°	2376	670
25°	436	219
35°	112	75
45°	31	25
55°	8	8
65°	3	3
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P743944
CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	9557.6
0.5°	9557.6
1°	9545.7
1.5°	9521.8
2°	9478.4
2.5°	9420.6
3°	9338.9
3.5°	9224.8
4°	9055.5
4.5°	8849.5
5°	8589.9
5.5°	8248.6
6°	7898.8
6.5°	7498.0
7°	7105.6
7.5°	6646.1
8°	6235.8
8.5°	5823.1
9°	5441.8
9.5°	5092.0
10°	4766.0
12.5°	3422.2
15°	2376.2
17.5°	1552.4
20°	978.7
22.5°	634.1
25°	435.8
27.5°	306.4
30°	220.4
32.5°	158.3
35°	112.3
37.5°	78.3
40°	56.2
42.5°	40.9
45°	30.6
47.5°	23.8
50°	16.2
52.5°	10.2
55°	7.7
57.5°	6.0
60°	4.3
62.5°	3.4
65°	2.6



TEST NUMBER: P743944
CATALOG NUMBER: LD4D20D010-EU4DR2015309024-4LBS1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





67.5°		1.7
70°		0.9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)