

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744735

Luminaire Tested: LD4D20D010-EU4DR7020359027-4LBDP1LI

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P744735
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR7020359027-4LBDP1LI
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR CLEAR TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1892.7 lumens
Efficiency: N/A
Efficacy: 81.9 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744735
CATALOG NUMBER: LD4D20D010-EU4DR7020359027-4LBDP1LI

Luminous Intensity Polar Plot





TEST NUMBER: P744735

CATALOG NUMBER: LD4D20D010-EU4DR7020359027-4LBDP1LI

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	232507
5°	225597
10°	219308
15°	216434
20°	202105
25°	151828
30°	107327
35°	38014
40°	19982
45°	21293
50°	22046
55°	22459
60°	22595
65°	22130
70°	20892
75°	19335
80°	17177
85°	13915

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 57.5°
 Luminance: 22613 cd/sqm



TEST NUMBER: P744735

CATALOG NUMBER: LD4D20D010-EU4DR7020359027-4LBDP1LI

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	194.0	10.3
10°-20°	532.2	28.1
20°-30°	586.1	31.0
30°-40°	223.9	11.8
40°-50°	105.7	5.6
50°-60°	105.1	5.6
60°-70°	84.2	4.4
70°-80°	48.3	2.6
80°-90°	13.2	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	1312.3	69.3
0°-40°	1536.2	81.2
0°-60°	1747.1	92.3
0°-90°	1892.7	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1892.7	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	2128	
5°	2057	194
15°	1913	532
25°	1259	586
35°	285	224
45°	138	106
55°	118	105
65°	86	84
75°	46	48
85°	11	13
90°	0	



TEST NUMBER: P744735

CATALOG NUMBER: LD4D20D010-EU4DR7020359027-4LBDP1LI

CANDELA DISTRIBUTION (FULL):

	0°
0°	2128.0
2.5°	2105.8
5°	2056.9
7.5°	2016.2
10°	1976.7
12.5°	1943.4
15°	1913.4
17.5°	1840.9
20°	1738.2
22.5°	1516.5
25°	1259.4
27.5°	1096.3
30°	850.7
32.5°	549.5
35°	285.0
37.5°	154.0
40°	140.1
42.5°	139.2
45°	137.8
47.5°	134.8
50°	129.7
52.5°	124.0
55°	117.9
57.5°	111.2
60°	103.4
62.5°	94.7
65°	85.6
67.5°	75.5
70°	65.4
72.5°	55.2
75°	45.8
77.5°	36.0
80°	27.3
82.5°	19.2
85°	11.1
87.5°	4.4
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)