

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269



Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745165

Luminaire Tested: LD4D25D010-EU4DR3520359040-4LBDP1MW

Issue Date: 1/30/2024

Test Information

Test Method: LM-79-2019
Report Number: P745165
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-20)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 1/30/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D25D010-EU4DR3520359040-4LBDP1MW
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 35° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 4000K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2315.3 lumens
Efficiency: N/A
Efficacy: 92.2 lumens/watt
Spacing Criteria (0/90/45): 0.6 / 0.6 / 0.54
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 25.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745165
CATALOG NUMBER: LD4D25D010-EU4DR3520359040-4LBDP1MW

Luminous Intensity Polar Plot





TEST NUMBER: P745165

CATALOG NUMBER: LD4D25D010-EU4DR3520359040-4LBDP1MW

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20																		
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																														
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																												
1	115	112	110	108	112	110	108	107	106	105	103	103	101	100	99	98	98	96																												
2	110	106	103	101	108	105	102	99	102	99	97	99	97	95	96	95	93	92																												
3	106	101	97	94	105	100	96	93	97	95	92	95	93	91	93	91	89	88																												
4	103	97	92	89	101	96	92	89	94	90	88	92	89	87	90	88	86	84																												
5	99	93	88	85	98	92	87	84	90	86	84	89	85	83	87	84	82	81																												
6	96	89	84	81	94	88	84	81	87	83	80	85	82	80	84	81	79	78																												
7	93	85	81	78	91	85	80	77	84	80	77	83	79	77	82	79	76	75																												
8	90	82	78	74	88	82	77	74	81	77	74	80	76	74	79	76	73	72																												
9	87	79	75	72	86	79	75	72	78	74	71	77	74	71	77	73	71	70																												
10	84	77	72	69	83	76	72	69	76	72	69	75	71	69	74	71	69	68																												

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	696067
5°	679708
10°	612601
15°	475479
20°	269683
25°	104920
30°	39149
35°	21461
40°	14021
45°	8529
50°	5439
55°	3848
60°	2797
65°	1525
70°	96
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 8529 cd/sqm



TEST NUMBER: P745165

CATALOG NUMBER: LD4D25D010-EU4DR3520359040-4LBDP1MW

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	570.0	24.6
10°-20°	1112.8	48.1
20°-30°	453.9	19.6
30°-40°	108.6	4.7
40°-50°	45.3	2.0
50°-60°	18.7	0.8
60°-70°	5.9	0.3
70°-80°	0.1	0.0
80°-90°	0.1	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2136.7	92.3
0°-40°	2245.3	97.0
0°-60°	2309.3	99.7
0°-90°	2315.3	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2315.3	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	6371	
5°	6197	570
15°	4204	1113
25°	870	454
35°	161	109
45°	55	45
55°	20	19
65°	6	6
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745165

CATALOG NUMBER: LD4D25D010-EU4DR3520359040-4LBDP1MW

CANDELA DISTRIBUTION (FULL):

0°	
0°	6370.7
2.5°	6332.5
5°	6197.3
7.5°	5927.7
10°	5521.6
12.5°	4949.7
15°	4203.5
17.5°	3290.8
20°	2319.4
22.5°	1479.0
25°	870.3
27.5°	491.9
30°	310.3
32.5°	217.8
35°	160.9
37.5°	124.4
40°	98.3
42.5°	75.7
45°	55.2
47.5°	41.4
50°	32.0
52.5°	25.4
55°	20.2
57.5°	16.3
60°	12.8
62.5°	9.4
65°	5.9
67.5°	2.1
70°	0.3
72.5°	0.3
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.3
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)