

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269



Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744870

Luminaire Tested: LD4D25D010-EU4DR1515309050-4LBS1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P744870  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-21)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D25D010-EU4DR1515309050-4LBS1MW  
Description: 4 INCH ROUND SHALLOW MATTE WHITE TRIM, WITH 15° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 5000K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2580.0 lumens  
Efficiency: N/A  
Efficacy: 102.8 lumens/watt  
Spacing Criteria (0/90/45): 0.22 / 0.22 / 0.23  
Luminous Opening: Vertical Cylinder (Dia: 0.35' x H: 0.35')  
CIE Type: Direct

Input Watts (W): 25.1  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P744870  
CATALOG NUMBER: LD4D25D010-EU4DR1515309050-4LBS1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P744870

CATALOG NUMBER: LD4D25D010-EU4DR1515309050-4LBS1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100						100													
1	116	114	112	111	113	112	110	109	108	107	106	104	103	103	101	100	100	98						98													
2	113	110	107	105	111	108	106	104	105	103	102	102	101	100	100	98	98	96						96													
3	110	106	103	101	108	105	102	100	103	100	99	100	99	97	98	97	96	94						94													
4	108	103	100	98	106	102	99	97	100	98	96	99	97	95	97	95	94	93						93													
5	106	101	98	95	104	100	97	95	98	96	94	97	95	93	96	94	92	92						92													
6	104	99	95	93	102	98	95	93	97	94	92	96	93	92	95	93	91	90						90													
7	102	97	94	91	101	96	93	91	95	93	91	94	92	90	93	91	90	89						89													
8	100	95	92	90	99	95	92	90	94	91	89	93	91	89	92	90	89	88						88													
9	99	93	90	88	98	93	90	88	92	90	88	92	89	88	91	89	88	87						87													
10	97	92	89	87	96	92	89	87	91	89	87	91	88	87	90	88	86	86						86													

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	3955211	3955211	3955211
5°	2324263	2294171	2312322
10°	693686	698547	709240
15°	172550	175911	170483
20°	51622	59780	52718
25°	18198	23183	18431
30°	6687	8806	6799
35°	3348	3783	3239
40°	2116	2322	2116
45°	1561	1666	1561
50°	1245	1245	1245
55°	1037	1037	1037
60°	835	835	835
65°	635	635	635
70°	541	541	541
75°	340	340	454
80°	236	236	236
85°	125	125	125

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 45°  
 Vertical Angle: 45°  
 Luminance: 1666 cd/sqm



TEST NUMBER: P744870

CATALOG NUMBER: LD4D25D010-EU4DR1515309050-4LBS1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1673.3	64.9
10°-20°	688.3	26.7
20°-30°	136.7	5.3
30°-40°	34.1	1.3
40°-50°	17.9	0.7
50°-60°	13.3	0.5
60°-70°	9.4	0.4
70°-80°	5.4	0.2
80°-90°	1.6	0.1
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2498.2	96.8
0°-40°	2532.4	98.2
0°-60°	2563.6	99.4
0°-90°	2580.0	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2580.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	35151	35151	35151	35151	35151	
5°	22870	22635	22574	22730	22753	1670
15°	1987	2024	2025	1990	1963	681
25°	234	265	298	263	237	123
35°	46	49	52	49	45	31
45°	22	22	24	22	22	17
55°	15	15	15	15	15	13
65°	9	9	9	9	9	9
75°	4	4	4	4	6	5
85°	2	2	2	2	2	2
90°	0	0	0	0	0	



TEST NUMBER: P744870

CATALOG NUMBER: LD4D25D010-EU4DR1515309050-4LBS1MW

**CANDELA DISTRIBUTION (FULL):**

	0°	22.5°	45°	67.5°	90°
0°	35151.2	35151.2	35151.2	35151.2	35151.2
2.5°	31707.8	31734.6	31745.0	31776.2	31892.3
5°	22870.1	22635.0	22574.0	22730.3	22752.6
7.5°	13547.4	13595.0	13769.1	13807.8	13667.9
10°	7434.4	7495.4	7486.5	7540.0	7601.1
12.5°	3802.0	3754.4	3739.5	3800.5	3715.7
15°	1986.6	2023.8	2025.3	1989.5	1962.8
17.5°	1068.4	1111.6	1183.0	1125.0	1035.7
20°	630.9	669.6	730.6	683.0	644.3
22.5°	389.9	421.1	464.3	427.1	395.8
25°	233.6	264.9	297.6	263.4	236.6
27.5°	138.4	165.2	186.0	163.7	136.9
30°	89.3	104.2	117.6	102.7	90.8
32.5°	62.5	68.5	74.4	68.5	62.5
35°	46.1	49.1	52.1	49.1	44.6
37.5°	35.7	38.7	40.2	37.2	34.2
40°	29.8	31.2	32.7	31.2	29.8
42.5°	25.3	26.8	26.8	26.8	25.3
45°	22.3	22.3	23.8	22.3	22.3
47.5°	19.3	19.3	20.8	19.3	19.3
50°	17.9	17.9	17.9	17.9	17.9
52.5°	16.4	16.4	16.4	16.4	16.4
55°	14.9	14.9	14.9	14.9	14.9
57.5°	13.4	13.4	13.4	13.4	13.4
60°	11.9	11.9	11.9	11.9	11.9
62.5°	10.4	10.4	10.4	10.4	10.4
65°	8.9	8.9	8.9	8.9	8.9
67.5°	8.9	8.9	8.9	8.9	8.9
70°	7.4	7.4	7.4	7.4	7.4
72.5°	6.0	6.0	6.0	6.0	6.0
75°	4.5	4.5	4.5	4.5	6.0
77.5°	4.5	4.5	4.5	4.5	4.5
80°	3.0	3.0	3.0	3.0	3.0
82.5°	3.0	3.0	3.0	3.0	3.0
85°	1.5	1.5	1.5	1.5	1.5
87.5°	0.0	0.0	0.0	0.0	0.0
90°	0.0	0.0	0.0	0.0	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report







— 0°-180°    - - 45°-225°    - - - - 90°-270°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)