

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P744759

Luminaire Tested: LD4D20D010-EU4DR7020359035-4LBDP1B

Issue Date: 2/5/2024

Test Information

Test Method: LM-79-2019
Report Number: P744759
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2307-078-73)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/5/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D20D010-EU4DR7020359035-4LBDP1B
Description: 4 INCH ROUND DEEP 45° CUTOFF SPECULAR BLACK TRIM, WITH 70° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 3500K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 1143.2 lumens
Efficiency: N/A
Efficacy: 49.5 lumens/watt
Spacing Criteria (0/90/45): 0.88 / 0.88 / 0.82
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 23.1
Input Voltage (V): NR
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P744759

CATALOG NUMBER: LD4D20D010-EU4DR7020359035-4LBDP1B

Luminous Intensity Polar Plot





TEST NUMBER: P744759
 CATALOG NUMBER: LD4D20D010-EU4DR7020359035-4LBDP1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100																			
1	112	109	106	103	110	107	104	102	103	101	99	99	97	96	95	94	93	91																			
2	106	100	95	91	103	98	94	90	95	91	88	92	89	86	89	87	85	83																			
3	100	92	87	82	98	91	86	81	88	84	80	86	82	79	83	80	78	76																			
4	94	86	80	75	92	85	79	74	82	77	73	80	76	73	78	75	72	70																			
5	89	80	74	69	87	79	73	69	77	72	68	75	71	67	74	70	67	65																			
6	85	75	68	64	83	74	68	64	73	67	63	71	66	63	70	66	62	61																			
7	80	70	64	59	79	70	64	59	68	63	59	67	62	59	66	62	58	57																			
8	77	66	60	56	75	66	60	56	65	59	55	64	59	55	63	58	55	53																			
9	73	63	57	52	72	62	56	52	61	56	52	60	55	52	60	55	52	50																			
10	70	59	53	49	69	59	53	49	58	53	49	57	52	49	57	52	49	48																			

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	140444
5°	136264
10°	132470
15°	130727
20°	122075
25°	91707
30°	64823
35°	22969
40°	12081
45°	12856
50°	13309
55°	13563
60°	13658
65°	13366
70°	12619
75°	11694
80°	10382
85°	8399

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 60°
 Luminance: 13658 cd/sqm



TEST NUMBER: P744759

CATALOG NUMBER: LD4D20D010-EU4DR7020359035-4LBDP1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	117.2	10.2
10°-20°	321.4	28.1
20°-30°	354.0	31.0
30°-40°	135.3	11.8
40°-50°	63.9	5.6
50°-60°	63.5	5.6
60°-70°	50.9	4.4
70°-80°	29.2	2.6
80°-90°	7.9	0.7
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	792.6	69.3
0°-40°	927.9	81.2
0°-60°	1055.2	92.3
0°-90°	1143.2	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	1143.2	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	1285	
5°	1242	117
15°	1156	321
25°	761	354
35°	172	135
45°	83	64
55°	71	63
65°	52	51
75°	28	29
85°	7	8
90°	0	



TEST NUMBER: P744759

CATALOG NUMBER: LD4D20D010-EU4DR7020359035-4LBDP1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	1285.4
2.5°	1271.9
5°	1242.4
7.5°	1217.7
10°	1194.0
12.5°	1173.8
15°	1155.7
17.5°	1111.9
20°	1049.9
22.5°	916.0
25°	760.7
27.5°	662.2
30°	513.8
32.5°	331.9
35°	172.2
37.5°	93.0
40°	84.7
42.5°	84.1
45°	83.2
47.5°	81.4
50°	78.3
52.5°	74.9
55°	71.2
57.5°	67.1
60°	62.5
62.5°	57.2
65°	51.7
67.5°	45.6
70°	39.5
72.5°	33.4
75°	27.7
77.5°	21.8
80°	16.5
82.5°	11.6
85°	6.7
87.5°	2.6
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)