

Scaled data based on original data using  
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-  
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745828

Luminaire Tested: LD4D30D010-EU4DR2015309027-4LBDP1MW

Issue Date: 2/2/2024

**Test Information**

Test Method: LM-79-2019  
Report Number: P745828  
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)  
Test Lab: COOPER LIGHTING SOLUTIONS  
Issue Date: 2/2/2024  
Manufacturer: COOPER LIGHTING SOLUTIONS  
Product Line: PORTFOLIO  
Catalog Number: LD4D30D010-EU4DR2015309027-4LBDP1MW  
Description: 4 INCH ROUND DEEP 45° CUTOFF MATTE WHITE TRIM, WITH 20° OPTIC  
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT  
Ballast/Driver: -

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 2533.1 lumens  
Efficiency: N/A  
Efficacy: 87.3 lumens/watt  
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36  
Luminous Opening: Circular (Dia: 0.35' x H: 0')  
CIE Type: Direct

Input Watts (W): 29  
Input Voltage (V): NR  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 24 FT




Downlight



TEST NUMBER: P745828

CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBDP1MW

### Luminous Intensity Polar Plot





TEST NUMBER: P745828

CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBDP1MW

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75

**AVERAGE LUMINANCE (cd/sqm):**

	0°
0°	1575289
5°	1421198
10°	797659
15°	405461
20°	171665
25°	79241
30°	41949
35°	22608
40°	12081
45°	7139
50°	4148
55°	2210
60°	1399
65°	1008
70°	415
75°	0
80°	0
85°	0

**MAXIMUM LUMINANCE 45°-90°:**

Horizontal Angle: 0°  
 Vertical Angle: 45°  
 Luminance: 7139 cd/sqm



TEST NUMBER: P745828

CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBDP1MW

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	1026.5	40.5
10°-20°	1010.8	39.9
20°-30°	330.2	13.0
30°-40°	112.4	4.4
40°-50°	37.8	1.5
50°-60°	11.4	0.4
60°-70°	3.8	0.2
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2367.5	93.5
0°-40°	2479.9	97.9
0°-60°	2529.1	99.8
0°-90°	2533.1	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2533.1	100.0

**CANDELA DISTRIBUTION:**

	0°	Flux
0°	14418	
5°	12958	###
15°	3584	1011
25°	657	330
35°	170	112
45°	46	38
55°	12	11
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745828

CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBDP1MW

**CANDELA DISTRIBUTION (FULL):**

	0°
0°	14417.7
0.5°	14417.7
1°	14399.7
1.5°	14363.7
2°	14298.3
2.5°	14211.0
3°	14087.7
3.5°	13915.7
4°	13660.2
4.5°	13349.5
5°	12957.9
5.5°	12443.1
6°	11915.4
6.5°	11310.7
7°	10718.9
7.5°	10025.6
8°	9406.8
8.5°	8784.1
9°	8208.9
9.5°	7681.3
10°	7189.6
12.5°	5162.4
15°	3584.5
17.5°	2341.7
20°	1476.4
22.5°	956.5
25°	657.3
27.5°	462.2
30°	332.5
32.5°	238.8
35°	169.5
37.5°	118.1
40°	84.7
42.5°	61.6
45°	46.2
47.5°	35.9
50°	24.4
52.5°	15.4
55°	11.6
57.5°	9.0
60°	6.4
62.5°	5.1
65°	3.9



TEST NUMBER: P745828  
CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBDP1MW

**CANDELA DISTRIBUTION (continued):**

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



— 0°-180°

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.6
70°		1.3

Signify Classified - Internal  
Cooper Lighting Solutions Photometric Lab  
1121 Highway 74 South  
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)