

Scaled data based on original data using
LM-79-2019 Approved Method: Electrical and Photometric Measurements of Solid-
State Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

Brand: PORTFOLIO

Report Number: P745829

Luminaire Tested: LD4D30D010-EU4DR2015309027-4LBS1B

Issue Date: 2/2/2024

Test Information

Test Method: LM-79-2019
Report Number: P745829
TEST IS SCALED FROM IESNA LM-79-08 TEST DATA (G1-2310-195-36)
Test Lab: COOPER LIGHTING SOLUTIONS
Issue Date: 2/2/2024
Manufacturer: COOPER LIGHTING SOLUTIONS
Product Line: PORTFOLIO
Catalog Number: LD4D30D010-EU4DR2015309027-4LBS1B
Description: 4 INCH ROUND SHALLOW SPECULAR BLACK TRIM, WITH 20° OPTIC
Light Source: (1) HIGH LUMEN LED 90CRI / 2700K CCT
Ballast/Driver: -

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2707.4 lumens
Efficiency: N/A
Efficacy: 93.4 lumens/watt
Spacing Criteria (0/90/45): 0.34 / 0.34 / 0.36
Luminous Opening: Circular (Dia: 0.35' x H: 0')
CIE Type: Direct

Input Watts (W): 29
Input Voltage (V): NR
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 24 FT




Downlight



TEST NUMBER: P745829
CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBS1B

Luminous Intensity Polar Plot





TEST NUMBER: P745829
 CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBS1B

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																
RCR																																					
0	119	119	119	119	116	116	116	116	111	111	111	106	106	106	102	102	102	100			100																
1	115	113	111	109	113	111	109	108	107	106	104	103	102	101	100	99	98	97	97	98	97																
2	111	108	105	102	109	106	104	101	103	101	99	100	99	97	98	96	95	94	94	98	94																
3	108	103	100	97	106	102	99	96	100	97	95	97	95	93	95	93	92	91	91	98	91																
4	105	99	96	93	103	98	95	92	96	93	91	95	92	90	93	91	89	88	88	93	89																
5	102	96	92	89	100	95	91	89	94	90	88	92	89	87	91	88	86	85	85	91	86																
6	99	93	89	86	98	92	88	86	91	87	85	90	87	84	88	86	84	83	83	88	84																
7	96	90	86	83	95	89	86	83	88	85	82	87	84	82	86	84	82	81	81	86	82																
8	94	87	83	81	93	87	83	80	86	83	80	85	82	80	84	82	80	79	79	84	80																
9	91	85	81	78	91	85	81	78	84	80	78	83	80	78	82	80	78	77	77	82	78																
10	89	83	79	76	88	82	79	76	82	78	76	81	78	76	81	78	76	75	75	81	76																

AVERAGE LUMINANCE (cd/sqm):

	0°
0°	1683654
5°	1518976
10°	852533
15°	433355
20°	183479
25°	84703
30°	44838
35°	24156
40°	12922
45°	7633
50°	4436
55°	2343
60°	1508
65°	1060
70°	447
75°	0
80°	0
85°	0

MAXIMUM LUMINANCE 45°-90°:

Horizontal Angle: 0°
 Vertical Angle: 45°
 Luminance: 7633 cd/sqm



TEST NUMBER: P745829

CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBS1B

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	1097.1	40.5
10°-20°	1080.3	39.9
20°-30°	352.9	13.0
30°-40°	120.1	4.4
40°-50°	40.4	1.5
50°-60°	12.2	0.4
60°-70°	4.0	0.1
70°-80°	0.2	0.0
80°-90°	0.0	0.0
90°-100°	0.0	0.0
100°-110°	0.0	0.0
110°-120°	0.0	0.0
120°-130°	0.0	0.0
130°-140°	0.0	0.0
140°-150°	0.0	0.0
150°-160°	0.0	0.0
160°-170°	0.0	0.0
170°-180°	0.0	0.0
0°-30°	2530.4	93.5
0°-40°	2650.6	97.9
0°-60°	2703.1	99.8
0°-90°	2707.4	100.0
90°-120°	0.0	0.0
90°-150°	0.0	0.0
90°-180°	0.0	0.0
0°-180°	2707.4	100.0

CANDELA DISTRIBUTION:

	0°	Flux
0°	15410	
5°	13849	###
15°	3831	1080
25°	703	353
35°	181	120
45°	49	40
55°	12	12
65°	4	4
75°	0	0
85°	0	0
90°	0	



TEST NUMBER: P745829
CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBS1B

CANDELA DISTRIBUTION (FULL):

	0°
0°	15409.5
0.5°	15409.5
1°	15390.3
1.5°	15351.9
2°	15281.9
2.5°	15188.6
3°	15056.9
3.5°	14873.0
4°	14600.0
4.5°	14267.9
5°	13849.4
5.5°	13299.1
6°	12735.2
6.5°	12088.9
7°	11456.3
7.5°	10715.3
8°	10053.9
8.5°	9388.4
9°	8773.7
9.5°	8209.7
10°	7684.2
12.5°	5517.5
15°	3831.1
17.5°	2502.9
20°	1578.0
22.5°	1022.3
25°	702.6
27.5°	494.0
30°	355.4
32.5°	255.2
35°	181.1
37.5°	126.2
40°	90.6
42.5°	65.9
45°	49.4
47.5°	38.4
50°	26.1
52.5°	16.5
55°	12.3
57.5°	9.6
60°	6.9
62.5°	5.5
65°	4.1



TEST NUMBER: P745829
CATALOG NUMBER: LD4D30D010-EU4DR2015309027-4LBS1B

CANDELA DISTRIBUTION (continued):

	0°
72.5°	0.0
75°	0.0
77.5°	0.0
80°	0.0
82.5°	0.0
85°	0.0
87.5°	0.0
90°	0.0

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Report Generated By 670245859 / DESKTOP-T8S5UU9

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report





— 0°-180°

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



67.5°		2.7
70°		1.4

Signify Classified - Internal
Cooper Lighting Solutions Photometric Lab
1121 Highway 74 South
Peachtree City, GA 30269

Scaled Data Report



(END OF REPORT)